



Part Number : [1300830231](#)
Product Description : Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/12 SOW, 9.14m (30.0') Cord Length
Series Number : 130083
Status : Active
Product Category : Electrical Reels
Engineering Number : 92411



Documents & Resources

Drawings
[1300830231_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--------------|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------------------|--|
| Status | Active |
| Category | Electrical Reels |
| Series | 130083 |
| Description | Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/12 SOW, 9.14m (30.0') Cord Length |
| Comments | Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag. |
| Enclosure Rating | NEMA 4 |
| NEMA Configuration | N/A |
| Product Name | POW-R-MITE |
| Type | Cable Reel |
| UPC | 78678879233 |

Agency

| | |
|-----|---------|
| CSA | LR29921 |
| UL | E22769 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 5.0A |
| GFCI | No |
| Lamp Wattage - Maximum | N/A |
| On/Off Switch | N/A |
| Voltage - Maximum | 600V |

Physical

| | |
|----------------|----------------|
| Bulb Included | N/A |
| Cable Length | N/A |
| Cable Movement | Ratchet Lock |
| Cord Length | 9.14m (30.0') |
| Cord Type | 16/12 SOW |
| Depth | 0.34m (13.50") |
| Drum Lock | Ratchet |

| | |
|--------------------------|-----------------------------|
| Duty | Industrial |
| Guide Arm | 5° increments over 270° Arc |
| Height | 0.37m (14.50") |
| Lamp Type | N/A |
| Material - Coating | Powder Coating |
| Material - Housing | Cast Aluminum |
| Mounting Style | Rigid |
| Net Weight | 18143.700/g |
| Number of Conductors | 12 |
| Packaging Type | Carton |
| Primary Cord/Cable Entry | 1" NPT |
| Retraction Weight | 1.8kg (4.0 lb) |
| Width | 328.42mm (12.930") |
| Wire Size (AWG) | 16 |

This document was generated on Jan 11, 2025