


X14SAV-LVDS New

 Print



Mini-ITX Embedded Motherboard
Intel® Core® Ultra 9/7/5 Series 2 Processors

Key Features

- 1. Intel® Core® Ultra 9/7/5 Series 2 Processor, Single Socket LGA-1851 supported, CPU TDP supports Up to 65W
 - 2. Up to 96GB Unbuffered ECC/non-ECC CSODIMM/SODIMM, clocked DIMM support up to 6400MT/s (with Core Ultra 9/7), in 2 slots
 - 3. 1 PCIe 5.0 x16 slot (16/NA or 8/8 or 8/4/4) 1 PCIe 4.0 x4 MCIO port 1 M.2 M-Key 2280 (PCIe 5.0 x4) 1 M.2 E-Key 2230 (PCIe 4.0 x1/USB 2.0)
 - 4. Dual 2.5 Gigabit LAN with Intel® Ethernet i226LM LAN controller [AMT/vPro]
 - 5. Intel® W880 Controller for 4 SATA3 (6 Gbps) ports; RAID 0,1,5,10
 - 6. 4 Independent Displays (1 24 bit LVDS, 2 DP 2.1 ports, 2 HDMI 2.1 ports)
 - 7. Supports 12V - 24V DC power input
- ...

Optimized Servers

[SYS-E201-14AR](#)

Specifications

Resources

Parts List

Standard Parts (Bulk Package)			
	Part Number	Qty	Description
I/O Cables	CBL-PWEX-1066	1	4-pinATX Power Signal Cable
I/O Shield	MCP-260-00200-0N	1	StandardI/O Shield
SATA cable	CBL-0044L • eStore	1	57.5 cm SATA FLAT S-S PBF

Standard Parts (Retail Package)			
	Part Number	Qty	Description
I/O Cables	CBL-PWEX-1066	1	4-pinATX Power Signal Cable
I/O Shield	MCP-260-00200-0N	1	StandardI/O Shield
QRG	MNL-2751-QRG	1	Motherboard Quick Reference Guide
SATA cable	CBL-0044L • eStore	1	57.5 cm SATA FLAT S-S PBF

Optional Parts			
	Part Number	Qty	Description
Active Heatsink	SNK-P0085A4	1	1UHeatsink
	SNK-P0092AP4-1	1	2UActive CPU Heat Sink for Intel Socket LGA1700 Platform
I/O Cables	CBL-CDAT-0685	1	COMcable 30cm
	CBL-CUSB-0621-1	1	DualUSB 3.0 (F) Type A Cable 70cm
	CBL-CUSB-0664	1	USB2.0Cable 2 ports, 40CM
	CBL-MCIO-1240QU2P-E	1	40cm MCIOx4 to U.2+PWR cable
	CBL-PWEX-1066	1	4-pinATX Power Signal Cable
	CBL-SAST-0933 • eStore	1	OcuLinkv 1.0 to 4x SATA 7-pin,INT, 50CM
	CBL-SAST-0956 • eStore	1	55CMOCuLink to U.2 Cable with Molex Power Header
Riser card	RSC-S-6G5	1	1ULHS Standard Riser card with one PCIe 5.0 X16 slot.,H
TPM security module (optional, not included)	AOM-TPM-9672H	1	SPITPM 2.0 using SLB9672 (Retail Pack)

Certain products may not be available in your region

English 

About Us

Company Profile
Green Computing
Investor Relations
Careers
Site Map
Glossary

News

Press Releases
Supermicro in the News
Product Reviews
Press Kits
Events
Webinars

Resources

Brochures
Product Briefs
Solution Briefs
Success Stories
Videos
White Papers
Thought Leadership
Validated Designs
MySupermicro
Data Center Stories

Support

Support Home
Onsite Services
Technical Support
RMA
System Management
Product Resources
Security Center
Warranty Policy
FAQs

Connect & Follow

Locations
Contact Us
Newsletter Sign-up

