Part Number : 638113800
Product Description : PremiumGrade Hand Crimp Tool for 10.00mm Mini-Fit Sr. Male and Female Terminals, 16-14 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools



Documents and Resources

Tooling Specifications

ATS-6381138HM-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for 10.00mm Mini-Fit Sr. Male and Female Terminals, 16-14 AWG
Comments	Prototype and field repair; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054660201
Warranty Disclaimer	CAUTION: Molex tooling crimp

Downloaded from Arrow.com.

	specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	428.885/zg

Applicable Parts

Description	Part Number
Mini-Fit Sr. Crimp Terminal, Female, 16-14 AWG, Tin (Sn), USE NYE LUBE ON MATING SURFACES	428150041
Mini-Fit Sr. Crimp Terminal, Female, 16-14 AWG, Gold (Au)	428150042
Mini-Fit Sr. Crimp Terminal, Female, 16-14 AWG, Silver (Ag)	428150144
Mini-Fit Sr. Crimp Terminal, Male, 16-14 AWG, Tin (Sn)	428170041
Mini-Fit Sr. Crimp Terminal, Male, 16-14 AWG, Gold (Au)	428170042
Mini-Fit Sr. Crimp Terminal, Male, 16-14 AWG, Tin (Sn)	428170141
Mini-Fit Sr. Crimp Terminal, Male, 16-14 AWG, Gold (Au)	428170142
Mini-Fit Sr. Crimp Terminal, Male,	428171044

Downloaded from Arrow.com.

16-14 AWG, Silver (Ag)	
Mini-Fit Sr. Crimp Terminal, Male, 16-14 AWG, Silver (Ag)	428171144

Downloaded from Arrow.com.