




Part Number : [2147205001](#)

Product Description : Zero-Hachi Crimp Terminal, Female, Matte Tin (Sn) Plating, 32-30 AWG, Reel

Series Number : 214720

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[2147205001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[2147209200-SPK-200.pdf](#)

[2147190000-PS-000.pdf](#)

[2241410000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	214720
Description	Zero-Hachi Crimp Terminal, Female, Matte Tin (Sn) Plating, 32-30 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	Zero-Hachi
UPC	195842348530

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Durability (mating cycles max)	20
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin

Net Weight	13.160/mg
Packaging Type	Reel
Plating min - Mating	1.000µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.44-0.50mm
Wire Size (AWG)	30, 32
Wire Size mm ²	0.03-0.05

Mates With / Use With

Use with Part(s)

Description	Part Number
Zero-Hachi Single Row Receptacle Housings	<u>214719</u>

Application Tooling

Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for Zero-Hachi Female Crimp Terminals, 32-28 AWG, UL 3767 Wire	<u>2130693600</u>
FA2 Pneumatic Feed Applicator for Zero-Hachi Female Crimp Terminals, 32-28 AWG, UL 3767 Wire	<u>2130693610</u>

Japan

Description	Part Number
S-1 Applicator for Zero-Hachi Wire-to-Board Crimp Terminals, 32-28 AWG, UL 3767 Wire	<u>2173623710</u>
Hand Crimp Tool for Zero-Hachi 0.80mm Pitch Crimp Terminals, 32-28 AWG, UL 3767 Wires	<u>2173625710</u>

This document was generated on May 21, 2026