

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-TX5e 28 AWG ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'UTP28CH10BU'

Your search criteria matched only one product, shown below

UTP28CH10BU



- Exceed requirements of ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D channel and component standards
- Small diameter, flexible cable design enables improved cable routing and management in high density applications; allows twice the amount of cables to be routed through cable managers and pathways when compared to traditional Category 5e patch cable
- Each patch cord is 100% performance tested and wired to T568A
- Constructed of Category 5e, 28 AWG stranded copper cable (nominal cable diameter is 0.149 in.(3.8mm) and Pan-Plug™M,3[Trade]™ Modular Plugs for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Labels on patch cords provide identification of performance level, length, and quality control number

- Patented tangle-free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 Plug Lock-In Device blocks unauthorized removal of cable, IP phone, other networking equipment or critical connection

• Part Number	UTP28CH10BU
• RoHS Compliancy Status	Compliant
• Part Description	Category 5e, 28 AWG UTP patch cord with Pan-Plug™ Modular Plugs on each end.
• Product Type	Copper Patch Cord
• Color	Blue
• Length (ft.)	10
• Length (m)	3.05
• Boot Color	No Boot
• Cable Color	Blue
• Cable Type	UTP
• CE Compliant	No
• Connector 1 Type	RJ45 8(8)
• Connector 2 Type	RJ45 8(8)
• Flammability Rating	CMLSZH
• Performance Level	Category 5e/Class D
• Pricing Description	Copper Patch Cord, Cat 5e, 28 AWG, Blue UTP Cable, 10 Feet
• Termination End 1	Modular Plug
• Termination End 2	Modular Plug
• Wiring Scheme	T568A
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.