

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039013043

Status:


Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit Jr.™ Plug Housing, Dual Row, 4 Circuits, UL 94V-2, without Panel Mounting Ears, Natural



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-45750-001-001 \(PDF\)](#)

[Product Specification PS-5556-001 \(PDF\)](#)

[Product Specification TS-5556-002-001 \(PDF\)](#)

[Packaging Specification PK-5559-002-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5559
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.
MolexKits	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit Jr.™
UPC	800755527988
Physical	
Breakaway	No
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.320/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	13.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	5559-04P1

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

5559 Series

Mates With

Receptacle Housing 39-01-3042

Receptacle Housing 39-01-2040

Mini-Fit Jr.™ TPA Cable Assembly 45135

Mini-Fit Jr.™ Cable Assembly 245135

Use With

5558 Mini-Fit Jr.™ Male Crimp Terminals.

30490 Mini-Fit® Male Grounding Crimp Terminals

Reference - Drawing Numbers

Packaging Specification	PK-5559-002-001
Product Specification	PS-45750-001-001, PS-5556-001, TS-5556-002-001
Sales Drawing	SD-5559-NP1*

This document was generated on 03/09/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION