

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Cable duct for installation and mounting in control cabinets, blue, halogen-free, comprising upper part and mounting base, width: 100 mm, height: 100 mm, length: 2000 mm

## Commercial Data

Item number	3240606
Packing unit	1 pc
Minimum order quantity	6 pc
Sales Key	BE74
Product Key	BE7442
Catalog Page	Page 579 (C-3-2019)
GTIN	4046356630221
Weight per Piece (including packing)	1,918 g
Weight per Piece (excluding packing)	1,918 g
Customs tariff number	39259020
Country of origin	DE

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>




## Technical Data

### Connection data

Nominal cross section	7391 mm <sup>2</sup>
-----------------------	----------------------

### Dimensions

Dimensional drawing	
Width	100 mm
Height	100 mm
Length	2000 mm

### Material specifications

Color	blue
Material	PC/ABS
Flammability rating according to UL 94	V0
Components	halogen-free

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------


# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## Drawings



Base perforation according to DIN EN 50085

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## Approvals



**CSA**

Approval ID: 248269



**VDE Zeichengenehmigung**

Approval ID: 40028972



**EAC**

Approval ID: RU C-DE.PB68.W.00513

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## Classifications

### ECLASS

ECLASS-11.0	27400703
ECLASS-12.0	27400703
ECLASS-13.0	27400703

### ETIM

ETIM 8.0	EC000012
----------	----------

### UNSPSC

UNSPSC 21.0	39131700
-------------	----------

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## Accessories

### RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

---

### RVT-PA 6 - Fastening clip

3240499

<https://www.phoenixcontact.com/us/products/3240499>



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

# CD-HF 100X100 BU - Cable duct

3240606

<https://www.phoenixcontact.com/us/products/3240606>



## UNIFOX-RVT P 4 - Tool

1212478

<https://www.phoenixcontact.com/us/products/1212478>

Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets



---

## UNIFOX-RVT P 6 - Tool

1212509

<https://www.phoenixcontact.com/us/products/1212509>

Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets



---

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)