



Part Number : [39000021](#)

Product Description : SPOX Crimp Terminal, 24-18 AWG, Phosphor Bronze, Reel

Series Number : 5194

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 5194PBT

Packaging Alternative : [39000022](#) (Bag)



Documents and Resources

Drawings

[039000021_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[51949200-200.pdf](#)

[PS-5195-005-001.pdf](#)


Tooling Specifications

[CS-5194-001.pdf](#)

[CS-5194\(S\)-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5194
Description	SPOX Crimp Terminal, 24-18 AWG, Phosphor Bronze, Reel
Application	Signal
Product Name	SPOX
UPC	800754318242

Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.20mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
SPOX 3.96mm Pitch Single Row Receptacle Housings	<u>5195</u>
SPOX 5.08mm Pitch Single Row Receptacle Housings	<u>5197</u>
SPOX 5.08mm Pitch Single Row Receptacle Housings	<u>5198</u>

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for SPOX Terminals, 24-18 AWG	<u>638116500</u>
Extraction and Activation Tool	<u>638132700</u>
FineAdjust Applicator for SPOX Crimp Terminal, Insulation Diameter OD 1.70-2.10mm, 24-18 AWG	<u>639044600</u>
FineAdjust Applicator for Insulation Diameter OD 2.20-2.60mm, 24-18 AWG	<u>639045200</u>
T2 Terminator for 3.96mm Pitch SPOX Crimp Terminal, 24-18 AWG	<u>639145200</u>

Japan

Description	Part Number
Hand Extraction Tool	<u>11260100</u>

S-1 Applicator for SPOX Terminals, 24-20 AWG	<u>2023013700</u>
S-1 Applicator for SPOX Terminals, 18 AWG	<u>2023013710</u>

This document was generated on Dec 29, 2025