



Color: ■ gray

Transformatorenklemmen Serie 711 mit CAGE CLAMP®

Die Transformatorenklemmen mit der Artikelnummer 711-132 ermöglichen eine einfache und zuverlässige Verbindung. Bei diesen Transformatorenklemmen ist für den Leiteranschluss eine Abisolierlänge im Bereich von 9 bis 10 mm nötig. Bei diesem Produkt findet die CAGE CLAMP®-Technologie Verwendung. Der zuverlässige und wartungsfreie CAGE CLAMP® Universalanschluss ermöglicht den Anschluss aller Leiterarten mit einer Käfigzugfeder. Eine Vorbehandlung der Leiter, z.B. durch das Aufcrimpen von Aderendhülsen, ist nicht erforderlich. Die Abmessungen sind in Breite x Höhe x Tiefe (15 x 35 x 23,5) mm.

Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated surge voltage	-	8 kV	-
Rated current	-	25 A	-

Connection data

Clamping units	2	Connection 1	
Total number of potentials	2	Connection technology	CAGE CLAMP®
Number of connection types	1	Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
		Pole number	2

Physical data

Width	15 mm / 0.591 inches
Height	35 mm / 1.378 inches
Depth	23.5 mm / 0.925 inches



Material data		
Note (material data)	Information on material specifications can be found here	
Color	gray	
Material group	I	
Insulation material (main housing)	Polyamide (PA66)	
Flammability class per UL94	V0	
Fire load	0.161 MJ	
Weight	7.5 g	

Commercial data		
PU (SPU)	50 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4044918819305	
Customs tariff number	85369010000	
End of Sale	2024-12-31	
End of Production	2025-10-01	
End of Delivery	2025-11-28	
End of Service and Repair	2026-12-01	

Product Classification		
UNSPSC	39121410	
eCl@ss 10.0	27-14-11-10	
eCl@ss 9.0	27-14-11-10	
ETIM 9.0	EC000398	
ETIM 8.0	EC000398	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant,No Exemption	

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
			Approval	Standard	Certificate Name
CCA	EN 60998	NTR NL-7194	EU-Declaration of Confor- mity	-	-
DEKRA Certification B.V.			WAGO GmbH & Co. KG		
CCA	EN 60998	2160584.54	UK-Declaration of Confor- mity	-	-
DEKRA Certification B.V.			WAGO GmbH & Co. KG		
CSA	C22.2 No. 158	1101145			
DEKRA Certification B.V.					
UL	UL 1059	E45172			
UL International Germany GmbH					



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 711-132			↓

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data			
CAD data		CAE data	
2D/3D Models 711-132		EPLAN Data Portal 711-132	↓
		ZUKEN Portal 711-132	↓