



Have a Question?  
Chat with a Product  
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Product Feature Selector > Product Details

2-1985835-5 Product Details

Share Print Email

2-1985835-5

TE Internal Number: 2-1985835-5

Active

Fiber Optic Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Duplex Fiber
- Cable Assembly
- FOKIT ODC™ Fiber Optic Cable Connector Type, LC Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = FOKIT ODC™ to LC Duplex

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
<div><div>Product Drawings:</div><ul style="list-style-type: none"><li>FIBER OPTIC ODC LEAD 2 FOLD PLUG - LC DUPLEX MULTI M... (PDF, English)</li></ul><div><div>Catalog Pages/Data Sheets:</div><ul style="list-style-type: none"><li>None Available</li></ul><div><div>Product Specifications:</div><ul style="list-style-type: none"><li>None Available</li></ul><div><div>Application Specifications:</div><ul style="list-style-type: none"><li>None Available</li></ul><div><div>Instruction Sheets:</div><ul style="list-style-type: none"><li>None Available</li></ul><div><div>CAD Files:</div><ul style="list-style-type: none"><li>None Available</li></ul></div></div></div></div></div></div>	<div><div>Related Products:</div><ul style="list-style-type: none"><li>Tooling</li></ul></div>
<a href="#">List all Documents</a>	

Product Features (Please use the Product Drawing for all design activity)	
<div><div>Product Type Features:</div><ul style="list-style-type: none"><li>Product Designation = Duplex Fiber</li><li>Product Type = Cable Assembly</li><li>Fiber Optic Cable Connector Type = FOKIT ODC™, LC</li><li>Cable Assembly Type = FOKIT ODC™ to LC Duplex</li><li>Cable Type = FOCAB ODC™</li></ul><div><div>Termination Features:</div><ul style="list-style-type: none"><li>Fiber Type (Micron) = 50/125</li></ul><div><div>Dimensions:</div><ul style="list-style-type: none"><li>Cable Diameter (mm [in]) = 5.50 [.216]</li><li>Length (M [ft]) = 25.00 [82.02]</li></ul><div><div>Body Features:</div><ul style="list-style-type: none"><li>Cable Color = Black</li><li>Connector Color = Beige, Black</li><li>Boot Body Style - Left = Standard</li><li>Boot Color - Left = Black</li><li>Boot Body Style - Right = Standard</li><li>Boot Color - Right = Beige</li><li>Protective Cap = With</li></ul></div></div></div></div>	<div><div>Contact Features:</div><ul style="list-style-type: none"><li>Fibre Channel = No</li></ul><div><div>Configuration Features:</div><ul style="list-style-type: none"><li>Mode = Multimode</li><li>Number of Fibers = 2</li><li>Cable Buffering = Tight Buffered</li><li>Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°</li></ul><div><div>Industry Standards:</div><ul style="list-style-type: none"><li>RoHS/ELV Compliance = RoHS compliant, ELV compliant</li><li>Lead Free Solder Processes = Not relevant for lead free process</li><li>RoHS/ELV Compliance History = Always was RoHS compliant</li></ul><div><div>Product Availability:</div><ul style="list-style-type: none"><li>Region = Not Specified</li></ul><div><div>Other:</div><ul style="list-style-type: none"><li>Brand = TE Connectivity</li></ul></div></div></div></div></div>

Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address