
CE PLAN EST UN DOCUMENT CONTROLE PAR TYCO ELECTRONICS CORPORATION.
IL EST SUSCEPTIBLE D'ETRE REVISE. POUR OBTENIR LA DERNIERE REVISION,
CONTACTER LE SERVICE TECHNIQUE DE TYCO ELECTRONICS SIMEL SAS
21220 GEVREY-CHAMBERTIN, FRANCE


THIS DRAWING IS A CONTROLLED DOCUMENT.


LOC	DIST
FH	00

REVISIONS


P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	G	AJOUT NOTA	07DEC2009	BG	GP
	H	ECR-11-018538	07SEP2011	LP	NA







Ces produits répondent à la norme NFC 20-130.
These products are NFC 20-130 compliant.



(L)	C	ØA	DESCRIPTION	PART NUMBER
58	13,5	8,3	XCT 70-8	710028-1
58	13,5	10,3	XCT 70-10	710028-3
58	13,5	12,8	XCT 70-12	710028-5
60,5	16,5	14,5	XCT 70-14	710028-6
60,5	16,5	16,5	XCT 70-16	710028-8

1 - MATERIAL = TINNED COPPER

2 - Marking in depth: logo-section-hole-Made in France +

3 - CABLE SECTION = 2/0 AWG or 70mm2

4 - GROOVE E70Cu OR DIE (Punch 17PC120+ Die 17M70)

TOLERANCES UNLESS OTHERWISE SPECIFIED -
TOLERANCES NON SPECIFIEES: -

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES (SUIV. NB DE DECIMALES):
0 PLC/DEC: ±0
1 PLC/DEC: ±0
2 PLC/DEC: ±0
3 PLC/DEC: ±0
4 PLC/DEC: ±0
ANGLES ±-

DWN/DESSINE 15DEC00 D.LEGUY
CHK/VERIFIE - E.DEREY
APVD/APPROUVE - N.ALMEIDA
PRODUCT SPEC SPEC. PRODUIT -
APPLICATION SPEC SPEC. APPLICATION -
WEIGHT MASSE APPROX.

MATERIAL MATIERE: CUIVRE
FINISH FINITION: ETAME

TE Connectivity

NAME TITRE: XCT 70-..

SIZE FORMAT: A4
CAGE CODE: 00779
DRAWING NO No PLAN: C-710028
RESTRICTED TO RESERVE A: -

CUSTOMER DRAWING /PLAN CLIENT UNIQUEMENT POUR REFERENCE
SCALE ECHELLE: - / -
SHEET FEUILLE: 1 OF DE: 1
REV: H

1469-35 (3/11)

RELEASED FOR PUBLICATION 20
LIBRE A LA DIFFUSION
ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.
THIS DRAWING IS UNPUBLISHED. -
DIFFUSION RESTREINTE
© COPYRIGHT 20

Downloaded from Arrow.com.