

EMG150-LG/O - Electronics housing



2906571
<https://www.phoenixcontact.com/us/products/2906571>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, for PCB insertion, without screw connection terminal blocks and cover, with open terminal space

Commercial data

Item number	2906571
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918131357
Weight per piece (including packing)	104 g
Weight per piece (excluding packing)	107.96 g
Customs tariff number	84879090
Country of origin	DE

EMG150-LG/O - Electronics housing

2906571

<https://www.phoenixcontact.com/us/products/2906571>




Technical data

Product properties

Product type	Complete housing
Housing type	Component housing
Housing series	EMG
Product family	EMG
Type	Lower part of housing, removable cover optional

Dimensions

Dimensional drawing	
Width	150 mm
Installed height	47.5 mm
Height NS 35/7,5	55 mm
	83 mm
Depth	75 mm
Length	75 mm

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PC (glass-fiber reinforced)
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


EMG150-LG/O - Electronics housing

2906571

<https://www.phoenixcontact.com/us/products/2906571>



Drawings




EMG150-LG/O - Electronics housing

2906571

<https://www.phoenixcontact.com/us/products/2906571>



Dimensional drawing




1 = Top edge of the PCB

B = Housing width

EMG150-LG/O - Electronics housing

2906571

<https://www.phoenixcontact.com/us/products/2906571>



EMG150-LG/O - Electronics housing



2906571

<https://www.phoenixcontact.com/us/products/2906571>

Classifications

ECLASS

ECLASS-13.0	27190101
ECLASS-15.0	27190101

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG150-LG/O - Electronics housing



2906571
<https://www.phoenixcontact.com/us/products/2906571>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com