



**Part Number :** [936011637](#)

**Product Description :** Heavy-Duty Standard (STD)  
Single Lever Hood, Die-cast Aluminum, with 2 Pegs,  
Top Entry, Size 10B «57x27», M32 Thread, High  
Construction, Grey

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Number :** 7810.6451.5



---

## Documents & Resources

### Drawings

[936011637\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                                                                              |
| REACH SVHC         | Not Contained per D(2021)10043-DC (17 Jan 2022)                                                              |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

|                |                                                                                                                                               |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                                        |
| Category       | Heavy Duty Connectors                                                                                                                         |
| Series         | 93601                                                                                                                                         |
| Description    | Heavy-Duty Standard (STD) Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 10B «57x27», M32 Thread, High Construction, Grey |
| Component Type | Single Lever Hood                                                                                                                             |
| IP Rating      | IP66                                                                                                                                          |
| Product Name   | Heavy-Duty Connectors                                                                                                                         |
| Standard       | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984                                                                                       |
| Type           | STD                                                                                                                                           |
| UPC            | 887191838922                                                                                                                                  |

### Agency

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

### Electrical

|                   |      |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

### Physical

|                |                  |
|----------------|------------------|
| Component Size | 10B «57X27»      |
| Entry Location | Top              |
| Hood Coating   | Polyester Powder |

|                     |                   |
|---------------------|-------------------|
| Hood Color          | GREY RAL 7037     |
| Lock to Mating Part | Yes               |
| Material - Hood     | Die-cast Aluminum |
| Material - Peg      | Stainless Steel   |
| Net Weight          | 196.000/g         |
| Number of Pegs      | 2                 |
| Packaging Type      | Bag               |
| Thread Size         | M32               |
| Thread Type         | (M) Metric        |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number                                                                                   |
|-------------|-----------------------------------------------------------------------------------------------|
| Use With    | Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts |

---

This document was generated on Sep 23, 2025