

Master Disconnect Switches

2 Terminals

Cole Hersee part number	Housing	Mounting stem	Large stud	Large contact	UL Rated	12V intermittent rating (Amps)	12V continuous rating (Amps)	Field circuit	O-ring in neck	Gasket in base	Bushing seal	Lever	Key	Locator pin	Lock-out
2484	Brass	Brass	Copper	Copper	Yes	125	40					Diecast			
2484-02	Steel	Brass	Silver	Silver		1000	175						Yes	Yes	
2484-03	Steel	Brass	Silver	Silver		1000	175		Yes				Yes	Yes	
2484-06	Steel	Brass	Silver	Silver		1000	175		Yes	Yes	Yes	Diecast		Yes	
2484-09	Steel	Brass	Copper	Copper		1000	175			Yes	Yes	Diecast			
2484-16	Steel	Brass	Silver	Silver	Yes	800	175					Diecast			
2484-19	Steel	Steel	Silver	Silver		1000	175		Yes	Yes	Yes		Yes		
2484-A	Steel	Brass	Silver	Silver		1000	175					Diecast			
75908	Steel	Steel	Copper	Copper		2000	300		Yes	Yes	Yes	Diecast		Yes	
75920	Plastic	Zinc	Tin/Copper	Silver		3000	300		Yes	Yes	N/A	Large Plastic		Yes	Yes
M-284	Brass	Brass				1000	175								
M-284-01	Brass	Brass				125	20								
M-284-02	Brass	Brass				1000	175								
M-284-A	Brass	Brass				1000	175								
M-288	Steel	Brass					50								

4 Terminals

Cole Hersee part number	Housing	Mounting stem	Large stud	Large contact	UL Rated	12V intermittent rating (Amps)	12V continuous rating (Amps)	Field circuit	O-ring in neck	Gasket in base	Bushing seal	Lever	Key	Locator pin	Lock-out
75904-01	Steel		brass	Silver		1000	175	Yes							
75904-02	Steel	Brass	Brass	Silver		1000	175	Yes							
75904-03		Brass				1000	175	Yes							
75903	Steel	Brass	Copper	Copper		1000	175	Yes	Yes	Yes		Bright Chrome			
75907	Steel	Steel	Copper	Copper		2000	300	Yes	Yes	Yes	Yes	Diecast		Yes	
75912	Steel	Steel	Brass	Silver		750 x 2	125 x 2		Yes	Yes	Yes	Diecast			
M-289	Brass	Brass				1000	125	Yes							
M-290	Brass	Brass				1000	125	Yes							
75904	Steel	Brass	Copper	Silver		1000	175	Yes				Diecast			