

**EOL Announced**

Recommended Alternate Part No. : [SPM10054T-220M-HZR](#) (Interchangeability is not guaranteed.)

**Product Status**

Discontinue Issue Date : May.14, 2024

Last Purchase Order Date : Mar.31, 2026

Last Shipment Date : Dec.31, 2026

**Applications**

Commercial Grade

**Wire Wound**Wire Wound

**Feature**

**Shield**Magnetic Shield

Ferrite CoreFerrite Core

**Series | Type**

SLF

**Brand**

TDK

**Environmental**

RoHS



REACH



Lead Free

**Compliance****Size**

Length(L)	12.50mm $\pm 0.30$ mm
Width(W)	12.50mm $\pm 0.30$ mm
Thickness   Height	6.50mm $\pm 0.35$ mm
Recommended Land Pattern (A)	2.60mm Nom.
Recommended Land Pattern (B)	8.50mm Nom.
Recommended Land Pattern (C)	3.20mm Nom.

**Electrical Characteristics**

Inductance	22 $\mu$ H $\pm 20\%$ at 1kHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	3.5A (10% Down)
Rated Current (Temperature Rise) [Typ.]	3.8A (40°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	31.6m $\Omega$
DC Resistance [Max.]	37.9m $\Omega$
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

**Other**

Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
-----------------------	--

! Images are for reference only and show exemplary products.







! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [330mm Reel]
Package Quantity	500pcs
Weight	3.2g

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.



! All specifications are subject to change without notice.

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.