

CATALOG LISTING

64AT44-3

1 OF 1

RELEASE NO. 203860

CHECK

REPLACES -

MICRO SWITCH

a Honeywell Division

FED. MFG. CODE 91929

ASSEMBLY-
TOGGLE SWITCH

CATALOG LISTING

64AT44-3

KEYWAY POSITION - MAINTAINED
C-NC MADE SWITCHES 1 & 2
C-NO MADE SWITCHES 3 & 4

OPPOSITE KEYWAY - MAINTAINED
C-NC MADE SWITCHES 3 & 4
C-NO MADE SWITCHES 1 & 2

34°±8°
TOTAL TRAVEL

17°±4°

.388±.010

.434

.072 WIDE X ▽.038 KEYWAY

.68

.47

.265±.015

.05

1.420 MAX

NC NO C C NO NC

1.100 MAX

SEE SWITCH OFFSET DETAIL

SWITCH NO.1

SWITCH NO.2

SWITCH NO.3

SWITCH NO.4

.320±.020

.320±.020

.670 MAX

.187±.020

.187±.020

.374±.020

.374±.020

.206±.020

Ø.240

15/32-32 UNS THREAD

2X HEX NUT .56 ACROSS FLATS X .08 THICK (TL-10632) 5

(3°)

CRES INTERNAL TOOTH LOCKWASHER
Ø.60 X (.018) THICK (TS-10013) 5

CRES KEYING WASHER Ø.72 X
.031 THICK, TAB .110 WIDE (TS-10020) 5

Ø .56 SHOULDER

.48

Ø.060 TYP

SWITCH OFFSET
DETAIL

.007

NOTES

1 - UNIT INCLUDES "SX" TYPE BASIC SWITCH (4)

2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY

3 - TERMINAL DESIGNATION MARKED ON BOTH SIDES OF UNIT

4 - DULL FINISH ON LEVER AND BUSHING

5 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805

6 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS

OPERATING FORCE

FORCE TO MOVE LEVER
FROM ONE POSITION TO ANY
ADJACENT POSITION, 1-5 LB
APPLIED .125±.030 BELOW
TOP OF LEVER

ELECTRICAL DATA

CONTACT ARRANGEMENT

4X S P D T

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT

DETAIL RATING CHART

VOLTS	CYCLE	AMPERES SEA LEVEL				AMPERES 50,000 FT			
		RES	IND			RES	IND		
28VDC		1.000	.50			1.000	.50		

ANSI Y14.5M-1982 APPLIES

PTC/CAD 2D

DRAWN

GRT 22 FEB 01

CHECK

NJ 22 FEB 01

Downloaded from Arrow.com