Part Number : 2157591042
Product Description : Micro-Fit+ Versa Color Receptacle Housing, Single Row, 2 Circuits, UL 94V-0, Glow-Wire Capable, Yellow
Series Number : 215759
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2157591042_sd.pdf

2157590003-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2064600001-AS-000.pdf

2159530000-PS-000.pdf

2064600001-TS-000.pdf

2157590005-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215759
Description	Micro-Fit+ Versa Color Receptacle Housing, Single Row, 2 Circuits, UL 94V-0, Glow-Wire Capable, Yellow
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit+ Versa Color
UPC	196823364266

Agency

CSA	LR19980

Physical

Circuits (maximum)	2
Color - Resin	Yellow
Flammability	94V-0

Downloaded from Arrow.com.

Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.347/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit+ Right-Angle, Single Row, Through Hole Headers	215760
Micro-Fit+ Vertical, Single Row, Through Hole Headers	216571
Micro-Fit+ Single Row Surface Mount Headers	218989

Use with Part(s)

Description	Part Number
Micro-Fit+ Female Crimp Terminals	206460
Micro-Fit+ Terminal Position Assurance (TPA) Retainers	206462

Downloaded from Arrow.com.