




Color: ■ gray

Module width	10	15	20	25
Component height	4.2	9.2	14.2	19.2
X = total height of PCB	8	13	18	23



Empty component plug housing, type 11

Electrical data	
Rated continuous current	6 A
Safety and protection	
Rated Voltage	250 V
Rated impulse withstand voltage	4 kV
Pollution degree	3
Connection data	
Pole number	8



Physical data		
Width		20 mm / 0.787 inches
Height		52 mm / 2.047 inches
Depth from upper-edge of DIN-rail		82.5 mm / 3.243 inches
Note (dimensions)		Depth including carrier terminal block

Mechanical data		
Housing design		Plug for carrier terminal blocks
Mounting type		Pluggable module for receptacle terminal blocks

Material data		
Color		gray

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		10 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4044918840118
Customs tariff number		85366990990

Product Classification		
UNSPSC		39121402
eCl@ss 10.0		27-18-27-02
eCl@ss 9.0		27-18-27-02
ETIM 9.0		EC001031
ETIM 8.0		EC001031
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 286-112

↓



CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 286-112	WSCAD Universe 286-112
	
	ZUKEN Portal 286-112
	

1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marker



Item No.: 209-701
WSB marking card; as card; not stretchable; plain; snap-on type; white

1.1.2 Terminal blocks
1.1.2.1 Terminal block for pluggable modules



Item No.: 280-638
Terminal block for pluggable modules; 8-pole; with 2-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray



Item No.: 280-764
Terminal block for pluggable modules; 8-pole; with 4-conductor terminal blocks; with marker carrier; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray



Item No.: 280-628
Terminal block for pluggable modules; 8-pole; with 4-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

1.1.3 Tool
1.1.3.1 Unlocking pliers



Item No.: 210-492
Unlocking pliers for component plug housing