Part Number : 2037021900
Product Description : FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Receptacle Terminal and SMEC Crimp Receptacle Terminals, 26-22 AWG and AVSS 0.3 Wires
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037021900-000.pdf

TM-638000029-001.pdf

TM-638004900-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for 2.00mm Pitch Wire-to-Board Crimp Receptacle Terminal and SMEC Crimp Receptacle Terminals, 26-22 AWG and AVSS 0.3 Wires
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust
Tool Type	Applicator
UPC	193264209484
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer.

Downloaded from Arrow.com.

	Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	1.000/g

Applicable Parts

Description	Part Number
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 26-22 AWG, Reel	503728000
2.00mm Pitch DuraClik Crimp Terminal, Female, 26-22 AWG, Gold (Au) Plating, Reel	561618081
DuraClik Crimp Terminal, Female, 26-22 AWG, Tin (Sn) Plating, Reel	5600850101

Downloaded from Arrow.com.