

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1451350210

Status:


Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit TPA2-to-Mini-Fit TPA2 Off-the-Shelf (OTS) Cable Assembly, Single Row, 1.0m Length, 2 Circuits, Black



Documents:	
3D Model	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

General	
Product Family	Cable Assemblies
Series	145135
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit TPA2 Both Ends
Overmolded	No
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit TPA2
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	191130113477
Physical	
Cable Length	1.0m
Circuits (Loaded)	2
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	34.332/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.98-3.14mm
Wire Size AWG	16
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	11.0A
Voltage - Maximum	600V AC/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	4000095324-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained per - D(2022)9120-DC (17 Jan 2023)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series	
145135 Series	
Mates With	
Mini-Fit TPA2 Plug Housing 200471 , 200488 Mini-Fit Jr. Plug Housing 5559 Mini-Fit Jr. Headers 5566 , 5569	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION