


55/2124-26-2/6-9 Product Details

[Share](#) [Print](#) [Email](#)


✓ Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

55/2124-26-2/6-9

55/2124-26-2/6-9

TE Internal Number: 625533-000

Product Highlights [View All](#)

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Flat Braid Shielded and Jacketed
- Wire Size (AWG/CM) = 26 AWG
- Voltage Rating = 600 VAC

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Cable Type [?]	Spec 55
Cable Style	Flat Braid Shielded and Jacketed

Electrical Characteristics

Voltage Rating (VAC)	600
----------------------	-----

Body Features

Wire Size (AWG/CM)	26 AWG
Cable Jacket Color	White
Conductor Type	Silver-Coated High Strength Copper Alloy
Wire Color	Red, Blue
Nominal Outside Diameter (mm [in])	2.21 [0.087]
Wire Diameter (mm [in])	0.81 [0.032]
Shield Size	36 AWG
Shield Material	Tin Plated Copper

Configuration Features

Number of Conductors	2
----------------------	---

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance [?]	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes [?]	Not relevant for lead free process

Conditions for Usage

Temperature Range (°C)	-65 - +200
------------------------	------------

Operation/Application

Application	Space Applications
-------------	--------------------

Packaging Features

Wire Source	United States
-------------	---------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

