

Product data sheet

Characteristics

AR3357

APC NetShelter SX, Server Rack Enclosure, 48U,
Black, 2258H x 750W x 1200D mm [TAA]



Commercial status

This Product is Obsolete :

⚠ This Product is Obsolete

Main

Product or Component Type	Rack enclosure
Number of rack unit	48U
Provided equipment	Baying hardware Key(S) Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Height	88.9 In (2258 mm)
Width	29.5 In (750 mm)
Depth	47.2 In (1200 mm)
Product Weight	408.85 Lb(US) (185.45 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	41.3 In (1048 mm)
Minimum Mounting Depth	10.3 In (261.9 mm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.6 kg) dynamic 3750 Lb(US) (1701.0 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

GTIN	731304259367
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	94.5 In (240 cm)
Package 1 Width	33.5 In (85.1 cm)
Package 1 Length	52.5 In (133.4 cm)
Package weight(Lbs)	444.94 Lb(US) (201.82 kg)

Compliance

Compliance	TAA Compliant BAA Compliant via COTS
------------	---

Environmental data

Recyclability potential, in %	95
Total lifecycle Carbon footprint	708 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	676.0139099848109
Carbon footprint of the manufacturing phase [A1 to A3]	676 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	17.102022543768488
Carbon footprint of the distribution phase [A4]	17 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	15.036872651690784
Carbon footprint of the end-of-life phase [C1 to C4]	15 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Carbon footprint (kg CO2 eq, Total Life cycle)	708
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
REACH Regulation	Reference contains Substances of Very High Concern above the threshold ↗
EU RoHS Directive	Compliant ↗
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	60
----------------------	----

Product Life Status : **End of commerc. announced**

AR3357 may be replaced by any of the following products:



AR3357B2

APC NetShelter SX Server Rack Gen 2, 48U, 2258H x 750W x 1200D mm, with Sides, Black [TAA]

Qty 1

Substitution date: |
