

Dual-Port USB Car Charger with 24W Charging - USB-C (24W) PD 3.0, USB-A (24W) QC 3.0, Black

MODEL NUMBER: U280-C02-24W-1B



2-port car charger quickly and safely charges 2 tablets, smartphones and other USB-C or USB-A devices at the same time.

Features

USB Car Charger Safely Charges 2 Mobile Devices in Your Vehicle Simultaneously This dual-port USB car charger with Power Delivery (PD) 3.0 and Quick Charge (QC) 3.0 technology lets you quickly and safely charge two USB mobile devices at the same time. You and a passenger can connect your smartphones, tablets, notebooks or power banks, to name just a few compatible devices, to ensure satisfactory battery charge when you reach your destination.

A Combined 24W of Charging Power Feeds Your Power-Hungry Devices When used together, the USB-C PD 3.0 and USB-A QC 3.0 ports support a total of 24W of charging power. Each fast-charging port also maxes out at 24W (5V 3A, 9V 2.67A or 12V 2A) individually to keep your USB-C tablet, USB-A smartphone and other devices at capacity. Instead of charging at a preset power level, the ports adjust to the appropriate power level to provide as much charge as your compliant device's battery can handle.

Plugs into the 12V DC Power Outlet in Your Vehicle The compact charger connects to any standard 12V DC vehicle power outlet, such as the one on your dashboard. Just plug it in, and connect your devices' USB cables for fast, convenient mobile charging. An easy-to-see blue LED indicates the charger is receiving power. The U280-C02-24W-1B is compatible with Apple (including iPhone), Android (including Samsung), Windows and Amazon devices with USB-A, USB-C or Thunderbolt 3 charging ports.

Highlights

- 2-port USB charger connects to the 12V DC power outlet in your car, truck or SUV
- Ideal for charging smartphones, tablets, e-readers and notebooks while traveling
- Maximum charging power output of 24W when both ports are charging at the same time
- Prevents overheating and overcharging to shield your essential device from damage
- USB-C Power Delivery 3.0 port charges up to 4x faster than conventional USB chargers

Applications

- Charge up to 2 smartphones, tablets, power banks, e-readers, notebooks or any other USB-A, USB-C or Thunderbolt 3 devices while driving to your destination

System Requirements

- Vehicle with standard 12V DC power outlet

Package Includes

- U280-C02-24W-1B Dual-Port USB Car Charger, Black

Specifications

OVERVIEW	
UPC Code	037332254092
Product Type	Car Charger
Charging Form Factor	Direct Plug-In
Device Compatibility	Phone; Tablet; Amazon Kindle

INPUT	
Nominal Input Voltage(s) Supported	12V DC
Input Connection Type	Automatic Vehicle Cigarette Lighter
Input Plug Type	Car Auxiliary Power Outlet
Product Length (in.)	1.99
Product Length (cm.)	5.05
Product Length (ft.)	0.17
OUTPUT	
Output Capacity (Watts)	24
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Number of Charging Ports	2
Total Charging Watts	24
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB-C: 24W, PD 3.0USB-A: 24W, QC 3.0
Charging Ports / Amps	(2) 3A
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC
Unit Dimensions (hwd / in.)	1.180 x 1.980 x 0.760
Unit Dimensions (hwd / cm)	3.0 x 5.05
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 86°F (0° to 30°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)

Operating Humidity Range	30% to 90% RH
Storage Humidity Range	10% to 90% RH
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	Car Cigarette Lighter
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB C (FEMALE)
INPUT TRANSFORMER	
Input Voltage	12V to 24V
FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
Quick Charge Compliant	3.0
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty