



YAE22G13, Nylon Ring Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22G13](#)

Nylon Ring Terminal For 26 - 20 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulation
- Brazed seam for a strong, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability, and holding power
- Smooth funnel entry for easy wire insertion

Application

Types YAE-G and YAE-N terminals are rated 105 Deg C and meet military standard AS25036 Class 2 and SAE-AS7928 requirements

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer
EU RoHS Indicator	No
Certification - UL Recognized	Yes
Industry Standard(s)	No
Buy America(n) Qualified	Military Specified (Mil-Spec)
Certification - ETL	Contact Manufacturer
Standards - Industry Standards Met	No
Standards - RoHS Compliance Status	Military Specified (Mil-Spec)
Certification - CSA Approved	CM
UL Listed	No


Conductor

Conductor - Copper Str Size	20 AWG
Conductor Size	26 - 20 AWG
Conductor - Copper Str Size Range	26 AWG - 20 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current



Voltage - Maximum 600 V

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Width inch	0.05 in
Dimension - Z inch	0.22 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Length Overall inch	0.74 in
Dimension - N inch	0.13 in

General

Insulation Type	Nylon
Trade Name	INSULUG™
Insulation	Y
Military Specification	MS25036
Sub Brand	INSULUG
Color Code	Amber
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	YAE-G
UPC 12 Digit	781810804643
UPC 14 Digit GTIN	00781810804643
Material	Copper
Plating Type	Tin
UPC	781810804643

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAE22G13-SPEC-EN | REV 4/2026