


SmartRack 4-Post Rack-Mount Installation Kit for Select UPS Systems, Side Mount

MODEL NUMBER: 4POSTRAILSM



Installs on the outside edges of your 4-post rack's vertical mounting rails as extra support for a rack-mount UPS system or other networking or power protection equipment 17.5 in. wide.

Description

The 4POSTRAILSM 4-Post Rack-Mount Installation Kit supports heavy UPS systems in your EIA-standard four-post rack. The two L brackets mount to the outside edges of the rack's vertical mounting rails - the edges facing the side panels - using the rails' square mounting holes. Attaching the 4POSTRAILSM to the side leaves your front and rear mounting holes free for equipment. The brackets support up to 250 lbs (113.4 kgs) and are compatible with four-post racks with a mounting depth of 16.5 to 21.5 inches. In addition to UPS systems, the 4POSTRAILSM is compatible with other heavy networking or power protection equipment with a rectangular chassis of 17.5 inches in width. Rack-attachment hardware for square-hole mounting is included.

Features

Extra Support for Heavy UPS Systems

- Installs on outside edges of rack's vertical mounting rails
- Compatible with EIA-standard 4-post racks with mounting depths of 16.5-21.5 in.
- Leaves front and rear mounting holes free for equipment
- Supports up to 250 lbs (113.4 kgs)
- Also supports other heavy networking or power protection equipment 17.5 in. wide
- Rack-attachment hardware for square-hole mounting included

Specifications

OVERVIEW	
UPC Code	037332191762
Accessory Type	Rackmount Kit
Accessory Class	Rack Accessories

Highlights

- Supports UPS systems in EIA-standard 4-post racks
- Supports up to 250 lbs (113.4 kgs)
- Compatible with mounting depths of 16.5-21.5 in.
- Leaves front and rear mounting holes free for equipment
- Includes rack-attachment hardware for square-hole mounting

Package Includes

- (2) L brackets
- (8) M6 screws
- (8) M6 cup washers
- (8) M6 cage nuts



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Shipping Dimensions (hwd / in.)	6.30 x 5.71 x 25.40
Shipping Dimensions (hwd / cm)	16.00 x 14.50 x 64.52
Shipping Weight (lbs.)	4.20
Shipping Weight (kg)	1.91
Unit Dimensions (hwd / in.)	3.250 x 3.000 x 23.000
Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.