
Part Number : 561349002
Product Description : Micro-One Female Crimp Terminal, 2.00mm Pitch, Matte Tin Plating, 28-26 AWG, Reel
Series Number : 56134
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

561349002_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2059790000-AS-000.pdf

SPK-56134-001-001.pdf

2059790000-PS-000.pdf

Tooling Specifications

2063233710ATP-E-000.pdf

2063233710ATP-J-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	56134
Description	Micro-One Female Crimp Terminal, 2.00mm Pitch, Matte Tin Plating, 28-26 AWG, Reel
Application	Wire-to-Board
Product Name	Micro-One
UPC	193264040322

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Net Weight	33.000/mg
Packaging Type	Reel

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.88-1.30mm
Wire Size (AWG)	26, 28
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-One Wire-to-Board Receptacle Housings	205979
Micro-One Single Row Receptacle Housings	212724

Application Tooling

Global

Description	Part Number
FineAdjust Applicator for Micro-One Wire-to-Board Terminal, 28-26 AWG (UL1007) Wires	2037026000
Hand Crimp Tool for MicroClasp Receptacle Crimp Terminals, 28-22 AWG, UL1007 Wires	2133090400

Japan

Description	Part Number
S-1 Applicator for 2.00mm Pitch Micro-One Receptacle Terminal, 28-26 AWG	2063233710

Downloaded from Arrow.com.