


**UL**<sup>®</sup>  
**US**



- **Computers**
- **Power supplies**
- **Appliances**
- **Fitness equipment**
- **Off-road vehicles**

**NOTE:** Specifications and materials listed above are for standard switches.  
For information on specific and custom switches, consult Customer Service Center.

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages G-74 thru G-76. For additional options not shown in catalog, consult Customer Service Center.




[www.ckswitches.com](http://www.ckswitches.com)

# DF Series Power Rocker Switches

SWITCH FUNCTION

| NO. POLES | MODEL NO. | SWITCH FUNCTION |        | CONNECTED TERMINALS |            | SCHEMATIC |
|-----------|-----------|-----------------|--------|---------------------|------------|-----------|
|           |           | POS. 1          | POS. 2 | POS. 1              | POS. 2     |           |
|           |           |                 |        |                     |            |           |
| SP        | DF52      | OFF             | ON     | OPEN                | 1-1A       | SPST<br>  |
| DP        | DF62      | OFF             | ON     | OPEN                | 1-1A, 2-2A | DPST<br>  |

Part Number shown DF62J12S215QA



Actuator shown in Pos. 1


| NO. POLES | MODEL NO. | POS. 1 | POS. 2 | POS. 3 | POS. 1 | POS. 2   | POS. 3               | SCHEMATIC                                             |
|-----------|-----------|--------|--------|--------|--------|----------|----------------------|-------------------------------------------------------|
|           |           |        |        |        |        |          |                      |                                                       |
| SP        | DF72      | OFF    | ON     | ON     | OPEN   | 1 / 2-2A | 1 / 2-1A<br>1 / 2-2A | <div>POS. 1</div> <div>POS. 2</div> <div>POS. 3</div> |

All models

ACTUATOR

ACTUATOR COLOR

J1 ROCKER



| OPTION CODE | ACTUATOR COLOR |
|-------------|----------------|
| 2           | BLACK          |
| 1           | WHITE          |

NOTE: Actuator finish: matte. Other colors available, consult Customer Service Center.




Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

# DF Series Power Rocker Switches


## HOUSING STYLE/COLOR

### S SUB-PANEL




NOTE: DF52 & DF62 models only.

### G2 ACTUATOR GUARD



NOTE: Not available with 'A' termination.  
Available in black only.

### P PANEL




NOTE: Not available with 'A' termination.  
Available in black only.

| OPTION CODE | HOUSING COLOR |
|-------------|---------------|
| 2           | (STD.) BLACK  |
| 1           | WHITE         |

NOTE: Housing finish: matte. Other colors available, consult Customer Service Center.


### PANEL MOUNTING

| PANEL THICKNESS            | DIM 'A'          |
|----------------------------|------------------|
| .029-.048<br>(0,74) (1,22) | 1.021<br>(25,93) |
| .048-.078<br>(1,22) (1,98) | 1.029<br>(26,14) |
| .078-.117<br>(1,98) (2,97) | 1.045<br>(26,54) |
| .075-.140<br>(1,91) (3,56) | 1.075<br>(27,31) |




## TERMINATIONS

### 15 QUICK CONNECT



DF72 Models Only


### A RIGHT ANGLE, PC THRU-HOLE



Actuator shown in Pos. 1

NOTE: DF52 and DF62 Models Only

### PC MOUNTING




Dimensions are shown: Inches (mm)

Specifications and dimensions subject to change

www.ckswitches.com

## DF Series Power Rocker Switches

P O -



**NOTE:** Orientation of actuator markings and terminals.

\*D, H, & P' marking options: marking color white, standard for all actuator colors except white. Marking color black, standard for white actuators. Consult Customer Service Center for other available marking colors.

| OPTION CODE | CONTACT AND TERMINAL MATERIAL | RATINGS |                                                                                                                                                                                                    |
|-------------|-------------------------------|---------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| QA          | SILVER 1,2                    | POWER   | 16 AMPS @ 125, 250 V AC; 1/4 HP @ 125 V AC; 1/2 HP @ 250 V AC; 6 AMPS @ 48 V DC (UL),<br>2 AMPS @ 60 V DC, 11 AMPS @ 30 V DC<br>16 AMPS @ 125, 250 V AC; 1/4 HP @ 125 V AC; 1/2 HP @ 250 V AC (UL) |


\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

All models 


All models 

## AVAILABLE HARDWARE

### Actuator Guard



Material: Nylon 6/6  
Finish: Matte



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change