

ME MAX 22,5 DKL TRANS - Housing cover

2890386

<https://www.phoenixcontact.com/us/products/2890386>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 22.6 mm, height: 75.25 mm, depth: 5.5 mm, color: transparent



Your advantages

- Easy, tool-free mounting

Commercial data

Item number	2890386
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHABZ
GTIN	4046356079266
Weight per piece (including packing)	4.85 g
Weight per piece (excluding packing)	4.85 g
Customs tariff number	85389099
Country of origin	DE

ME MAX 22,5 DKL TRANS - Housing cover



2890386

<https://www.phoenixcontact.com/us/products/2890386>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 22,5..
Ventilation openings present	no

Dimensions

Width	22.6 mm
Height	75.25 mm
Depth	5.5 mm

Material specifications

Color	transparent
Color (Housing)	transparent
Flammability rating according to UL 94	V2
CTI according to IEC 60112	250
Insulating material	IIIa
Housing material	PC
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

ME MAX 22,5 DKL TRANS - Housing cover

2890386

<https://www.phoenixcontact.com/us/products/2890386>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2890386>



UL Recognized

Approval ID: E240868

ME MAX 22,5 DKL TRANS - Housing cover



2890386

<https://www.phoenixcontact.com/us/products/2890386>

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME MAX 22,5 DKL TRANS - Housing cover



2890386
<https://www.phoenixcontact.com/us/products/2890386>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com