

VPB-1/4-0-SP Product Details

 Share  Print  Email



 Active

Heat Shrink Tubing

VPB-1/4-0-SP

VPB-1/4-0-SP 

TE Internal Number: 5580564002

Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = VPB
- Product Source = U.K., U.S.
- Flexible
- Medium Wall Style

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through Distributor 

 Feedback

Documents

Features

 Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type 	Heat Shrinkable Tubing
Color	Black

Dimensions	
Expanded ID, Min. (mm [in]) 	6.40 [0.252]
Recovered ID, Max. (mm [in]) 	3.20 [0.126]

Body Features	
Product Name	VPB
Pliancy	Flexible
Wall Style 	Medium
Wall Type 	Single
Material	Polymer Blend Fluoroelastomer
Shrink Ratio 	2:1

Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Lubricating Oil, Unleaded Gasoline
Resistant To	Abrasion, Fluids, Wrinkling
Wall Thickness - Full Recovery (Nominal) (mm [in])	0.88 [0.0346]

Housing Features	
Material Systems	Yes
Material Systems Code 	30

Industry Standards	
Government/Industry Qualification	No
Flammability Rating	Flame-Retardant
UL Rating	None
CSA Certified	No
Approved Standards	SC-X-15111
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental	
Fluid Resistance	Splash Protection
Operating Temperature (°C) 	-55 – +150

Conditions for Usage	
Full Recovery Temperature (°C)	175
Shrink Temperature, Min. (°C)	100
High Temperature Compatible	Yes

Operation/Application	
Emission Free	No
Product Use	Cables, Harnesses
Application	Cable Jacketing, Wire Bundling

Packaging Features	
Packaging Method	Spool

Product Availability	
Product Source	U.K., U.S.

Other	
Brand	Raychem

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

Distributor Inventory

Product Cross Reference

Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Knowledge Base

Manage Your Account

Keep Me Informed

