

Home → Tool Types → Reversible Blades Drive Loc → Drive-Loc VI Hex Metric Nut Driver Blades

Drive-Loc VI Hex Metric Nut Driver Blades



Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

Be the first to review this product

Filter:

SKU	Product	Price	Qty
28168	Drive-Loc VI Nut Driver Hex 4.0 x 150mm		0
28169	Drive-Loc VI Nut Driver Hex 4.5 x 150mm		0
28170	Drive-Loc VI Nut Driver Hex 5.0 x 150mm		0
28171	Drive-Loc VI Nut Driver Hex 5.5 x 150mm		0
28172	Drive-Loc VI Nut Driver Hex 6.0 x 150mm		0
28173	Drive-Loc VI Nut Driver Hex 7.0 x 150mm		0
28174	Drive-Loc VI Nut Driver Hex 8.0 x 150mm		0
28177	Drive-Loc VI Nut Driver Hex 9.0 x 150mm		0

SKU	Product	Price	Qty
28175	Drive-Loc VI Nut Driver Hex 10.0 x 150mm		0
28176	Drive-Loc VI Nut Driver Hex 11.0 x 150mm		0

Add to Cart

Add to Wishlist

Share on Facebook

Tweet This

Pin it

We accept

Details

Drive-Loc VI Features Adjustable/Reversible Locking Blades
Selectable Lengths from 1.7" to 4.8" in 1/8" Increments
Wiha special chrome-vanadium-molybdenum tool steel
Through hardened for best wear resistance
Wiha ChromTop Finish on tip for a perfect fit every time

Additional Info

Head Type	nut driver metric
Country of Manufacture	Germany

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

View Full Warranty

You may also be interested in the following product(s)

Drive-Loc VI Hex Inch Blades

Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels

assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Discounts and promotions](#)

[Military Discount](#)

[IBEW-NECA Discount](#)

[Filter and sort all Wiha hand tools](#)

[Complete list of tools](#)

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

amazon pay

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh](#)
[Schonach Germany](#)

**Monday - Friday Office Hours 7am - 5pm
CST USA**

1348 Dundas Cir,
Monticello, MN 55362
Customer Service Email:
cservice@wihatools.com
Tel: 763-295-6591
Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools
In Stock**



Newsletter [Subscribe](#)