


CES-STPG-GY-6 - Cable sleeve



0801676
<https://www.phoenixcontact.com/us/products/0801676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 5 mm ... 6 mm, material: SEBS (halogen-free), color: gray, length: 29.5 mm, width: 19.5 mm, height: 17 mm

Product description

Slotted cable sleeve

Commercial data

Item number	0801676
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CCX
GTIN	4046356674829
Weight per piece (including packing)	7.84 g
Weight per piece (excluding packing)	7.84 g
Customs tariff number	40169997
Country of origin	PL

CES-STPG-GY-6 - Cable sleeve

0801676

<https://www.phoenixcontact.com/us/products/0801676>




Technical data

Product properties

Product type	Cable sleeve
No. of conductors	1

Dimensions

Dimensional drawing	
Width	19.5 mm
Height	17 mm
Length	29.5 mm

Material specifications

Material	SEBS (halogen-free)
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	1x 5 mm ... 6 mm
-------------------------	------------------

Characteristics

Seal size	small
Design, Format	Round cable
Design, Cable seal	slotted

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 80 °C (static)

CES-STPG-GY-6 - Cable sleeve


0801676

<https://www.phoenixcontact.com/us/products/0801676>



Drawings

Dimensional drawing



Dimensional drawing

CES-STPG-GY-6 - Cable sleeve



0801676

<https://www.phoenixcontact.com/us/products/0801676>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801676>



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026

DNV
Approval ID: TAE00003VJ

CES-STPG-GY-6 - Cable sleeve



0801676
<https://www.phoenixcontact.com/us/products/0801676>

Classifications

ECLASS

ECLASS-13.0	27144425
ECLASS-15.0	27144425

ETIM

ETIM 9.0	EC000451
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CES-STPG-GY-6 - Cable sleeve



0801676
<https://www.phoenixcontact.com/us/products/0801676>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.058 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com