



JavaScript seems to be disabled in your browser.

You must have JavaScript enabled in your browser to utilize the functionality of this website.

Wiha Tools Canada  selling **Wiha** made hand tools in Canada since 2007



IBEW-NECA  
DISCOUNT



**1-866-494-0096** 



Cart ▾

[Account](#) | [Log In](#) [Contact Us](#) | [Distributors](#)

[Wiha Tools No Hassle Guarantee](#)

 **Menu**

**Torx**



**Torque Tools**



**Tech Tools**



**Shop Tools**



**Screwdrivers**



**Pliers**



**Insulated Tools**



**Hex**



**ESD Safe**



**Bits & Sets**



**Best Sellers**

[Home](#) → [Insulated Tools](#) → [Insulated Electrical Tool Kits](#) → [Insulated Pliers/Cutters/Screwdrivers 11 Piece Set](#)

## **Insulated Pliers/Cutters/Screwdrivers 11 Piece Set**





Zoom

*Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.*

Insulated 6.3" Long Nose, 6.3" Stripping Pliers, 8" Combo Pliers, 6.3" Side Cutters, Slotted 2.5-6.0 & Philips #0-2 Screwdrivers in roll up pouch. 11 Pieces

**SKU:** 32888

[Add to Cart](#)

Qty:

[Share on Facebook](#)  [Tweet This](#)  [Pin it](#)

## Frequently bought together



[Add selected to cart](#)

**This item:** Insulated Pliers/Cutters/Screwdrivers 11 Piece Set

General Purpose Zipper Bag

## Details

### Screwdrivers:

Slotted: 2.5, 3.5, 4.5, 6.0mm

Phillips: #0, #1, #2

Meets ASTM F1505, VDE 0682/part201, DIN 7437, EN/IEC 60900, NFPA-70E & CSA specification

10,000 Volt Tested for a 1,000(AC) 1,500(DC) Volt Certification, VDE and GS tested

Ergonomic Wiha SoftFinish multi-component handle with roll-off protection  
Cushioned Grip For maximum comfort and power

Perfect fit for your Hand because of Wiha handle size concept

Wiha special chrome-vanadium-molybdenum tool steel

Through hardened for best wear resistance

Precision machined exact fit Black tips

### Pliers:

## Additional Info

SKU	32888
Weight (lbs)	3.5800
Packaging	Box
PROP 65	yes
Head Type	slotted, phillips
Handle Grip Types	Insulated SoftFinish®
UPC	084705328881
UNSPSC	27112135

8" Lineman's Pliers, 6.3" Diagonal Cutter, 6.3" Stripping Pliers  
Meets ASTM , EN/IEC, NFPA, CSA, VDE & OSHA's  
10,000 Volt Tested 1000 Volt Rated  
High Quality forged C70 Tool Steel  
Induction Hardened Cutting Edges and Jaws  
Ergonomic Molded Two Component Soft Comfort Grips  
Molded in Slip guards for added user protection  
Finger jam protection for safe operation at all settings

## Wiha Professional Quality Hand Tools



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure products consistent with our reputation for outstanding performance in demanding service, repair and production applications.

[Download Catalogs](#)

[Discounts and promotions](#)

[Filter and sort all Wiha hand tools](#)

## Wiha Tools Canada Ltd. Since 2007

Wiha Canadian operations started bringing Wiha quality to professional tool users in 2007 with a warehouse located in Brampton, Ontario and sales office in the Greater Toronto Area.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Check the status of your order](#)

[Having technical issues with the website?](#)

## Wiha Tools Canada Ltd.

A wholly owned Subsidiary of Willi Hahn Corporation

**Monday - Friday office hours 8AM - 5PM  
CST USA**

**No products are stocked at this location**

394 Deerhurst Drive

Brampton, ON, L6T 5H9

Customer Service Email: [info@wihatools.ca](mailto:info@wihatools.ca)

Tel: **1(866) 494-0096**

Fax: 1(800) 494-7456

GST/HST number Business Number: 82851

5551 RT0001

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools In Stock**



© 2018 Wiha Tools Canada. All Rights Reserved.

