


1469077-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1469077-1

Z-PACK HM-Zd Connectors and Cable Assemblies

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

Product Highlights:

- Connector
- Connector Assembly
- 20.3 mm Card Slot Pitch
- PCB Mounting Orientation = Right Angle
- Contact Type = Socket

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 1469077-1

Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)


Documentation & Additional Information

| | |
|---|--|
| <p>Product Drawings:</p> <ul style="list-style-type: none"> • RECEPTACLE ASSEMBLY, 2 PAIR, 50mm, HMZd (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • Two, Three and Four Pair HM-Zd Connectors (PDF, English) <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version E) • 3D Model (IGES, Version E) • 3D Model (STEP, Version E) | <p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling |
|---|--|

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

| | |
|--|--|
| <p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Connector • Connector Type = Connector Assembly • PCB Mounting Orientation = Right Angle • Shield Material = Phosphor bronze <p>Termination Features:</p> <ul style="list-style-type: none"> • Contact Termination Type = Through Hole • Interface Type = HM-Zd • Termination Method = Press Fit • Termination End Plating = Tin-Lead over Nickel <p>Dimensions:</p> <ul style="list-style-type: none"> • Card Slot Pitch (mm [in]) = 20.3 [0.8] • Module Length (mm [in]) = 49.90 [1.966] <p>Body Features:</p> <ul style="list-style-type: none"> • Columns per Connector = 20 • Selectively Loaded = No | <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Type = Socket • Contact Configuration = ACTION PIN Post • Contact Base Material = Copper-Nickel-Silicon <p>Housing Features:</p> <ul style="list-style-type: none"> • Centerline (mm [in]) = 2.50 [0.098] • Housing Material = Polyester GF <p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Pairs per Column = 2 • Number of Pairs per Connector = 40 • Number of Positions = 80 <p>Industry Standards:</p> <ul style="list-style-type: none"> • AdvancedTCA Specified Product = No • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP |
|--|--|

| | | | |
|--|---|---|--|
| <p>Corporate Information</p> <ul style="list-style-type: none"> About TE Investors News Room Supplier Portal Careers Terms & Conditions Privacy Policy | <p>Quick Links</p> <ul style="list-style-type: none"> Check Distributor Inventory Cross Reference Products Find Documents & Drawings Product Compliance Support Center Site Map | <p>Customer Support</p> <ul style="list-style-type: none"> Email or Chat With Us Find a Phone Number Search Knowledge Base Manage Your Account | <p>Keep Me Informed</p> <p>Receive TE News, Events & Technology Updates</p> <input type="text" value="Enter your email address"/>  |
|--|---|---|--|

