Part Number : 350230009
Product Description : 2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 9 Circuits, Natural
Series Number : 35023
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

350230009_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PK-35023-001-001.pdf

PS-35023-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35023
Description	2.00mm Pitch, Board-In Crimp Housing, Right-Angle and Vertical, 9 Circuits, Natural
Application	Wire-to-Board
Product Name	Board-in
UPC	800753876675

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-0
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.180/g

Downloaded from Arrow.com.

Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00mm Pitch, Board-in Crimp Terminal, Male, Vertical, Brass Pre-Plated Tin, 28-24 AWG, Reel	350449102
2.00/2.50mm Pitch, Board-in Crimp Terminal, Male, Right-Angle, Brass Pre-Plated Tin, 30-24 AWG, Reel	350211201
2.00/2.50mm Pitch, Board-in Crimp Terminal, Male, Right-Angle, Phosphor Bronze Pre-Plated Tin, 30-24 AWG, Reel	350211301
2.00/2.50mm Pitch, Board-in Crimp Terminal, Male, Right-Angle, Phosphor Bronze Post-Plated Tin, 30-24 AWG, Reel	350211360

Downloaded from Arrow.com.