




22759/34-10-5 Product Details

[Share](#)
[Print](#)
[Email](#)

Spec 44, Spec 55 and Spec RCW Wire and Cable


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

22759/34-10-5

TE Internal Number: 709026-000


[Obsolete](#)
[Contact Product Information Center](#)
[View all Features](#)
[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED...](#) (PDF, English)

Related Products:

- [Tooling](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Cable Type](#) = Spec 55
- [Cable Style](#) = Primary
- Number of Conductors = 1

Conditions for Usage:

- Temperature Range (°C) = -65 - +150
- Wire Size - Details = 10 AWG 4.74 mm², 0.0074 in², 37 x 26 AWG

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Operation/Application:

- Application = Airframe - Medium Weight

Body Features:

- Wire Size (AWG/CM) = 10 AWG
- Conductor Type = Tin-Plated Copper
- Wire Color = Green
- Nominal Outside Diameter (mm [in]) = 3.25 [0.128]
- Wire Diameter (mm [in]) = 3.25 [0.128]
- Conductor O.D. (mm [in]) = 2.81 [0.111]

Packaging Features:

- Wire Source = United States

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M22759/34-10-5
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Raychem

Corporate Information
[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
Quick Links
[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)
Customer Support
[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)
Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

