

G 20/0.50A/F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

For protection against overcurrent, we offer cartridge fuse with dimensions 5x20 mm in sizes from 100 mA to 6.3 A.

General ordering data

Version	Miniature fuse, quick-acting, 0.5 A, G-Si. 5 x 20
Order No.	0430600000
Type	G 20/0.50A/F
GTIN (EAN)	4008190046835
Qty.	10 pc(s).

G 20/0.50A/F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	20 mm	Height (inches)	0.787 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	0.9 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Cartridge fuse	G-Si. 5 x 20	Characteristics	quick-acting
Colour	Light Grey	Current	0.5 A
Melting integral	0.23 A²s	Optical function display	No
Power output (@ 1.5 In)	1 W	Rated breaking capacity	1.5 kA
Version	Fuse accessories	Voltage drop	600 mV

Rating data

Rated voltage	250 V	Rated current	0.5 A
---------------	-------	---------------	-------

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ETIM 10.0	EC002704	ECLASS 9.0	27-14-20-01
ECLASS 9.1	27-14-20-01	ECLASS 10.0	27-14-20-01
ECLASS 11.0	27-14-20-01	ECLASS 12.0	27-14-20-01
ECLASS 13.0	27-14-20-01	ECLASS 14.0	27-14-20-01
ECLASS 15.0	27-14-20-01		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Creation date May 24, 2025 2:37:49 AM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.