

UM-BE 35 - Base element



2955577

<https://www.phoenixcontact.com/us/products/2955577>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element without snap foot, for aligning several base elements with ribs, L = 35 mm



Commercial data

Item number	2955577
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
GTIN	4017918085544
Weight per piece (including packing)	17.72 g
Weight per piece (excluding packing)	17 g
Customs tariff number	85369010
Country of origin	PL

UM-BE 35 - Base element



2955577

<https://www.phoenixcontact.com/us/products/2955577>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM BE
Type	Plug-in module base element
Ventilation openings present	no

Dimensions

Width	35 mm
Depth	111 mm

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UM-BE 35 - Base element

2955577

<https://www.phoenixcontact.com/us/products/2955577>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2955577>



UL Recognized

Approval ID: E240868

UM-BE 35 - Base element



2955577

<https://www.phoenixcontact.com/us/products/2955577>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-BE 35 - Base element



2955577
<https://www.phoenixcontact.com/us/products/2955577>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com