

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| GP | 00 |


REVISIONS

| # | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | A1 | REVISED PER ECO-09-021480 | 08OCT2009 | CR | DG |



1888862-4
AS SHOWN











FIGURE M



1888862-8
AS SHOWN








FIGURE N

| FIGURE | CONNECTOR PART NUMBER | G | F | E | D | A | POSN | PART NUMBER |
|---|---|---|---|---|---|---|---|---|
| M | 1761987-2 | 3.5 | 36 | 17.8 | 16 | 18.05 | 36 | 1-1888862-6 |
| M | 1761987-2 | 2.8 | 36 | 17.8 | 16 | 18.05 | 36 | 1-1888862-2 |
| N | 1761987-2 | - | 36 | 17.8 | 16 | 18.05 | 36 | 1888862-8 |
| M | 1761987-2 | 2 | 36 | 17.8 | 16 | 18.05 | 36 | 1888862-4 |

1. MATERIAL: NICKEL-SILVER PER ASTM B 122.
2. SHELL ASSEMBLY TO BE USED WITH THE SURFACE MOUNT RECEPTACLE CONNECTOR PART NUMBER REFERENCED IN TABLE
3. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER

THIS DRAWING IS A CONTROLLED DOCUMENT AND IS THE EXCLUSIVE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS LOANED SUBJECT TO RETURN UPON REQUEST. ITS CONTENTS ARE NOT TO BE COPIED OR DISCLOSED WITHOUT WRITTEN AUTHORIZATION AND SHOULD BE CONTROLLED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES, UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.1
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: 1

FINISH: 2

DWN B. MCMASTER 21FEB07
CHK D. GORENC 21FEB07
APVD D. GORENC 21FEB07
PRODUCT SPEC 108-2234
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

Tyco Electronics
Tyco Electronics
Harrisburg, PA 17105-3608

NAME: EVERCLEAR Mini-SAS INTERNAL SHELL, RIGHT ANGLE RECEPTACLE, UNKEYED

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-1888862 | - |

SCALE 1:1 SHEET 1 OF 2 REV A1

ANP 4805 REV 31MAR2000


Downloaded from Arrow.com

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| GP | 00 |

REVISIONS

| # | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | - | SEE SHEET 1 | - | - | - |




RECOMMENDED PCB LAYOUT
SCALE 10:1

THIS DRAWING IS A CONFIDENTIAL DOCUMENT AND TYCO ELECTRONICS CORPORATION ("T.E.C.") EXPECTS ITS CONFIDENTIAL NATURE TO BE MAINTAINED. DISTRIBUTION SHOULD BE CONFINED TO THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.1
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES +/-

MATERIAL -
FINISH -

DWN B. MCMASTER 21FEB07
CHK D. GORENC 21FEB07
APVD D. GORENC 21FEB07
PRODUCT SPEC 108-2234
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
EVERCLEAR Mini-SAS INTERNAL SHELL, RIGHT ANGLE RECEPTACLE, UNKEYED

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A1 | 00779 | C-1888862 | - |

SCALE 5:1 SHEET 2 OF 2 REV A1

ANP 48055 REV 31MAR2000

Downloaded from Arrow.com.