

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Protecting Covers

## General Information

<b>Extended Product Type:</b>	PL10
<b>Product ID:</b>	1SNK900621R0000
<b>EAN:</b>	3472599097520
<b>Catalog Description:</b>	PL10 Protecting Cover - Transparent
<b>Long Description:</b>	- Prohibit access to the screw clamps, - Indicate live circuits.

## Ordering

<b>Color:</b>	Transparent
---------------	-------------

<b>Minimum Order Quantity:</b>	10 piece
--------------------------------	----------

<b>Customs Tariff Number:</b>	39269097
-------------------------------	----------

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160021D0201
---	-----------------

<b>Instructions and Manuals:</b>	1SNK160027C0201
----------------------------------	-----------------

## Dimensions

<b>Product Net Width:</b>	10 mm
---------------------------	-------

<b>Product Net Height:</b>	54.1 mm
----------------------------	---------

<b>Product Net Length:</b>	25.83 mm
----------------------------	----------

<b>Product Net Depth / Length:</b>	25.8 mm
------------------------------------	---------

<b>Product Net Weight:</b>	3.1 g
----------------------------	-------

## Technical

<b>Spacing:</b>	10 mm
-----------------	-------

<b>Function:</b>	Protecting Covers
------------------	-------------------

<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

<b>Insulation Material:</b>	Polycarbonate
-----------------------------	---------------

<b>Recommended Screw Driver:</b>	4 mm
----------------------------------	------

<b>Suitable For:</b>	ZS16 ZS25 ZS25-PE
----------------------	-------------------------

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V2
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230500F0202

Classifications

Object Classification Code:	X
E-nummer:	2925169

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	158 mm
Package Level 1 Depth / Length:	243 mm
Package Level 1 Gross Weight:	0.031 kg
Package Level 1 EAN:	3472599097520
Package Level 2 Units:	1000 piece
Package Level 3 Units:	48000 piece
Product Packing Type:	Bag

