BA16E10, Vinyl Ring Terminal, 22-16 AWG, #10 Stud



By Burndy
Catalog # BA16E10

Vinyl Insulated Copper Ring Terminal, 22-16 AWG, #10 Stud, Bulk Packaged

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Application

For Commercial, Light Duty Industrial Control and Power Circuit Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size Range	• 20 AWG -22 AWG • 16 AWG -18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	• 20 AWG - 22 AWG • 16 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.32 in
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Length	0.85 in
Dimension - Z inch	0.26 in
Height	0.32 in
Dimension - Length Overall inch	0.85 in
Dimensions	0.85 in x 0.32 in x 0.32 in

General

Product Family	COMPRESSION
Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Yes
Physical Attribute - Tongue Type	Ring
Sub Brand	VINYLUG
Product Type	Terminal
UPC	781810026700
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026700
UPC 14 Digit GTIN	00781810026700

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved

Downloaded from Arrow.com.