Part Number : 194130107
Product Description : Solderless Terminals Kit, Vinyl Insulated Ring Terminals, 300 Pieces
Series Number : 19413
Status : Active
Product Category : Kits
Engineering Part Number : KIT-MX12



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Kits
Series	19413
Description	Solderless Terminals Kit, Vinyl Insulated Ring Terminals, 300 Pieces
Comments	Includes 25 of each part number in the kit. See Kit Components below for links to included parts.
Component Type	Kit
Kit Component Parts	InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 27.40mm, Yellow, Carton, InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 27.40mm, Yellow, Carton, InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Length 31.60mm, Yellow, Carton, InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Length 34.30mm, Yellow, Carton, InsulKrimp Ring Tongue Terminal for 16-14 AWG Vinyl, Stud Size 0.25", InsulKrimp Ring Tongue Terminal for 16-14 AWG Vinyl, Stud Size 6 (M4), InsulKrimp Ring Tongue Terminal for 16-14 AWG, Vinyl, Stud Size 8, InsulKrimp Ring Tongue Terminal for Heavy Duty 16-14 AWG Wire, Vinyl, InsulKrimp Ring Tongue Terminal for 22-18 AWG, Vinyl, Stud Size 6, InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Vinyl, Stud Size 8, InsulKrimp Ring Tongue Terminal for 22-18 AWG, Vinyl, Stud Size 0.25", InsulKrimp Ring Tongue Terminal for 22-18 AWG

Downloaded from Arrow.com.

	Heavy Duty Wire, Vinyl, Stud Size 10 (M5)
Product Name	Solderless Terminals Kit
UPC	191128415347

Physical

Circuits (Loaded)	N/A
Depth	45.00mm
Length	280.00mm
Width	172.00mm

Kit Component Parts

Description	Part Number
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 8 (M4), Length 27.40mm, Yellow, Carton	190700121
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 27.40mm, Yellow, Carton	190700123
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 1/4" (M6), Length 31.60mm, Yellow, Carton	190700132
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Length 34.30mm, Yellow, Carton	190700153
InsulKrimp Ring Tongue Terminal for 16-14 AWG Vinyl, Stud Size 0.25"	190540086
InsulKrimp Ring Tongue Terminal for 16-14 AWG Vinyl, Stud Size 6 (M4)	190540081
InsulKrimp Ring Tongue Terminal for 16-14 AWG, Vinyl, Stud Size 8	190540110
InsulKrimp Ring Tongue Terminal	190540113

Downloaded from Arrow.com.

for Heavy Duty 16-14 AWG Wire, Vinyl	
InsulKrimp Ring Tongue Terminal for 22-18 AWG, Vinyl, Stud Size 6	190540033
InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Vinyl, Stud Size 8	190540037
InsulKrimp Ring Tongue Terminal for 22-18 AWG, Vinyl, Stud Size 0.25"	190540042
InsulKrimp Ring Tongue Terminal for 22-18 AWG Heavy Duty Wire, Vinyl, Stud Size 10 (M5)	190540039

Downloaded from Arrow.com.