Part Number : 847021006
Product Description : Double End IP67 Bayonet, 1.83m (6.0') Length
Series Number : 84702
Status : Obsolete
Product Category : Industrial Cable Assemblies



Documents and Resources

Drawings

847021006_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	84702
Description	Double End IP67 Bayonet, 1.83m (6.0') Length
Comments	Industrial Type, Gray Cable
IP Rating	IP67
Product Name	Brad,RJ-Lnxx
Type	Double Ended
UPC	822348117345

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Cable Diameter	6.35mm (.250")
Cable Length	1.83m (6.0')
Color - Cable Jacket	Black
Connector End A	RJ-45 (industrial)
Connector End B	RJ-45 (industrial)
Coupling Style	Snap
Gender	Male-Male
Keyway	None
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	Polypropylene
Material - Contact	Phosphor Bronze
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold

Obsolete

Downloaded from Arrow.com.

Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Shielded PVC
Wire Size (AWG)	24

Mates With / Use With

Mates with Part(s)

Description	Part Number
Industrial Ethernet RJ-45 Receptacle, Panel Mount	847000001
Receptacle, RJ-45, PCB Mount Receptacle	847020005
Receptacle, RJ-45, PCB Mount Receptacle Jack, Potted	847020007
Receptacle, RJ-45, Punchdown Panel Mount Receptacle Jack	847020006
Receptacle, RJ-45, Punchdown Panel Mount Receptacle Jack, Potted	847020008

Obsolete

Downloaded from Arrow.com.