











1393359-2	V23540-M1075-Y120	reinorange /RAL 2004 PURE ORANGE	PBT GF20 1)	3 g
TE-PN	EC-Bestell-Nr.	Farbe ähnlich: COLOR SIMILAR	Werkstoff MATERIAL	Gewicht WEIGHT
TE-PN	EC CODE NO.			



2-1393387-9	A	V23540-M1050-0800	Kurzschlußbrücke/SHORTING BAR	-	CuNi35Mg h	12	3	8g
Winkel/BACKET			weiss /WHITE ACC TO RAL 9010	PBT/ASA GF20 or PBT GF20 1)	1	2		
Buchsengehäuse/SOCKET HOUSING			reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	1	1		
TE-Assy-PN	TE-Rev.	EC Bestell-Nr.	Beschreibung	Farbe ähnlich	Werkstoff	Anzahl	Item-Nr.	Gewicht
TE-ASSY-PN	TE-REV	EC CODE-NO.	DESCRIPTION	COLOR SIMILAR	MATERIAL	NUMBER/ITEM-NR	WEIGHT	



4-1411095-5	A	-	C-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				Lichtblau/LIGHT BLUE RAL 5012	PBT GF20 1)	1		
4-1411095-4	A	-	H-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				olivgrün/OLIVE GREY RAL 7002	PBT GF20 1)	1		
4-1411095-3	A	-	G-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				melonengelb/MELON YELLOW RAL 1028	PBT GF20 1)	1		
4-1411095-2	A	-	L-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				signalblau/SIGNAL BLUE RAL 5005	PBT GF20 1)	1		
4-1411095-1	A	-	D-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				ultramarinblau/ULTRAMARINEBLUE RAL5002	PBT GF20 1)	1		
4-1411095-0	A	-	F-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				laubgrün/LEAF GREEN RAL 6002	PBT GF20 1)	1		
3-1411095-9	A	-	A-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				reseda-grün/RESEDA GREEN RAL 6011	PBT GF20 1)	1		
3-1411095-8	A	-	B-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				brilliantblau/BRILLIANT BLUE RAL 5007	PBT GF20 1)	1		
3-1411095-7	A	-	C-E	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				platingrau/PLATINUM GREY RAL 7036	PBT GF20 1)	1		
3-1411095-6	A	-	G-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				verkehrsblau/TRAFFIC BLUE RAL 5017	PBT GF20 1)	1		
3-1411095-5	A	-	C-D	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				verkehrsrot/TRAFFIC RED RAL 3020	PBT GF20 1)	1		
3-1411095-4	A	-	A-F	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				blau/BLUE RAL 5005	PBT GF20 1)	1		
3-1411095-3	A	-	B-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				gelborange/YELLOW ORANGE RAL2000	PBT GF20 1)	1		
3-1411095-2	A	-	E-F	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				erikaviolett/HEATHER VIOLET RAL 4003	PBT GF20 1)	1		
3-1411095-1	A	-	A-B	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				hellfliederblau/LIGHT LAVENDER RAL 5015	PBT GF20 1)	1		
3-1411095-0	A	-	G-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				pastellgelb/PASTEL YELLOW RAL 1034	PBT GF20 1)	1		
TE-Assy-PN	TE-Rev.	EC Bestell-Nr.	Kodierung	Beschreibung	Werkstoff	Item-Nr.	Gewicht	
TE-ASSY-PN	TE-REV	EC CODE-NO	CODING	DESCRIPTION	MATERIAL	ITEM NO.	WEIGHT	

		REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN	APVD	
	A20	ECR-18-005108			18APR2018	AN	KK	
	A21	ECR-23-162662			01APR2024	MG	MBK	

2-1411095-9	A	-	C-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				Rose / ROSE RAL 3017	PBT GF20 1)	1		
2-1411095-8	A	-	E-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				Licht grau/LIGHT GREY RAL 7035	PBT GF20 1)	1		
2-1411095-7	A	-	A-C	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				tiefschwarz/JET BLACK RAL 9005	PBT GF20 1)	1		
2-1411095-6	A	OBSELETE	F-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				verkehrsorange/TRAFFIC ORANGE RAL2009	PBT GF20 1)	1		
2-1411095-5	A	OBSELETE	C-F	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				signal violett/SIGNAL VIOLET RAL4008	PBT GF20 1)	1		
2-1411095-4	A	-	B-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				rotbraun/RED BROWN RAL 8012	PBT GF20 1)	1		
2-1411095-3	A	V23540-M1075-Y223	D-E	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				perlweiss/OSTER WHITE RAL 1013	PBT GF20 1)	1		
2-1411095-2	A	-	A-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				braunbeige/BROWN BEIGE RAL 1011	PBT GF20 1)	1		
2-1411095-1	A	-	D-F	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				lehtbraun/LAY BROWN RAL 8003	PBT GF20 1)	1		
2-1411095-0	A	-	B-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				beige/BEIGE RAL 1001	PBT GF20 1)	1		
1-1411095-9	A	-	D-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				beigegrau/BEIGE GREY RAL 7006	PBT GF20 1)	1		
1-1411095-7	A	V23540-M1075-Y220	E-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				patinagrün/PATINA GREEN RAL 6000	PBT GF20 1)	1		
1-1411095-6	A	-	A-E	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				tannengrün/FIR GREEN RAL 6009	PBT GF20 1)	1		
1-1411095-5	A	-	B-F	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				weissgrün/PASTEL GREEN RAL 6019	PBT GF20 1)	1		
1-1411095-4	A	-	C-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				schwarzoliv/BLACK OLIVE RAL 6015	PBT GF20 1)	1		
1-1411095-3	A	OBSELETE	D-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				moosgrün/MOSS GREEN RAL 6005	PBT GF20 1)	1		
1-1411095-2	A	V23540-M1075-Y219	A-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				lichtblau/LIGHT BLUE RAL 5012	PBT GF20 1)	1		
1-1411095-1	A	V23540-M1075-Y218	F-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				currygelb/CURRY RAL 1027	PBT GF20 1)	1		
1-1411095-0	A	V23540-M1075-Y232	H-L	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				blaugrau/BLUE GREY RAL 7031	PBT GF20 1)	1		
1411095-9	A	V23540-M1075-Y231	D-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				lichtgrün/LIGHT GREEN RAL 6027	PBT GF20 1)	1		
1411095-8	A	V23540-M1075-Y230	E-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				taubenblau/DOVE BLUE RAL 5014	PBT GF20 1)	1		
1411095-7	A	OBSELETE	F-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				weinrot/WINE RED RAL 3005	PBT GF20 1)	1		
1411095-6	A	V23540-M1075-Y216	A-C	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				lichtgrau/LIGHT GREY RAL 7035	PBT GF20 1)	1		
1411095-5	A	OBSELETE	B-K	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				unkistblau/TURQUOISE BLUE RAL 5018	PBT GF20 1)	1		
1411095-4	A	OBSELETE	B-C	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				nußbraun/NUT BROWN RAL 8011	PBT GF20 1)	1		
1411095-3	A	V23540-M1075-Y229	A-D	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				pastellrot/PASTEL VIOLET RAL 4009	PBT GF20 1)	1		
1411095-2	A	V23540-M1075-Y228	F-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				ozeanblau/OCEAN BLUE RAL 5020	PBT GF20 1)	1		
1411095-1	A	V23540-M1075-Y227	B-D	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				lachsrot/SALMON PINK RAL 3022	PBT GF20 1)	1		
1-1393362-2	A	V23540-M1075-Y215	B-E	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				hellrosa/LIGHT PINK RAL 3015	PBT GF20 1)	1		
1-1393362-1	A	V23540-M1075-Y205	D-G	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				signalgrün/SIGNAL GREEN RAL 6032	PBT GF20 1)	1		
1-1393362-0	A	V23540-M1075-Y204	C-H	Hebel/LEVER	reinorange/PURE ORANGE RAL 2004	PBT GF20 1)	2	14.3g
Abdeckkappe/COVER				verkehrsblau/TRAFFIC YELLOW RAL 1023	PBT GF20 1)	1		
TE-Assy-PN	TE-Rev.	EC Bestell-Nr.	Kodierung	Beschreibung	Werkstoff	Item-Nr.	Gewicht	
TE-ASSY-PN	TE-REV	EC CODE-NO	CODING	DESCRIPTION	MATERIAL	ITEM NO.	WEIGHT	

1) Regeneratanteil /RECYCLED MATERIAL : max 25% Liquideinfärbung zugelassen / LIQUID COLOR ALLOWED		Diese TE-Zeichnung ersetzt EC-Zeichnung V23540-M1075-Y200-*-7427 THIS TE-DRAWING REPLACED EC-DRAWING V23540-M1075-Y200-*-7427	
*) Längen : DIN 16901-130; Winkel, Form und Lage: DIN ISO 2768 mH/ LENGTH: din 16901-130; ANGLES, FORM AND POSITION: DIN ISO 2768 mH			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CH: Van Hoek	15NOV2000
DIMENSIONS: mm		CHK B. Reis	15NOV2000
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. Glaser	15NOV2000
MATERIAL		PRODUCT SPEC	
FINISH		APPLICATION SPEC	
WEIGHT			
CUSTOMER DRAWING			

NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
Massbild - DIMENS. DRAWING 75 polige Buchsenleiste Markt 12 KS	A1	00779	©=1411101	
SCALE	1:1	SHEET	1 of 2	REV A21

