

CATALOG NO.	DESCRIPTION	CHARGER CATALOG NO.
PAT444SL5	PAT444SL5 WITH 110V CHARGER	PATCHGRLI
PAT444SL5DC	PAT444SL5 WITH DC CHARGER	PATCHGRLIDC
PAT444SLI	PAT444SLI WITH 110V CHARGER	PATCHGRLI
PAT444SLIDC	PAT444SLI WITH DC CHARGER	PATCHGRLIDC
PAT444SLILCCB	PAT444SLI LESS CASE CHARGER AND BATTERY	--
PAT444SLILCB	PAT444SLI LESS CHARGER AND BATTERY	--

*** BILL OF MATERIAL PAT444SL5, LI ***			
PT NO.	CATALOG NO.	QTY	DESCRIPTION
1	PATCASELI	1	CASE, TOOL PATRIOT LITHIUM-ION
2	BATI8V5AHLI	2	BATTERY, MAKITA 18V LI-ION 5.0 AH MAKITA P/N BLI850B
2	BATI8VLI	2	BATTERY, MAKITA LITHIUM-ION 18V
3	PATCHGRLI	1	CHARGER, BATTERY LITHIUM-ION
4	BATCHGRLIOMI	1	BATTERY CHARGER SAFETY OPERATING MAINTENANCE & INSTRUCTIONS
5	PT208620	1	LANYARD
6	PAT444SL5OMI	1	SOMI, PAT444SL5
7	PT2044380I	1	FIVE YEAR WARRANTY CARD
8	LIMSDS	1	MSDS, LITHIUM-ION BATTERY

PATRIOT®

BATTERY ACTUATED TOOL - HYDRAULIC SELF CONTAINED - 11 TON OUTPUT FORCE


SPECIFICATIONS

CRIMP FORCE: 11 TONS (10.0 METRIC TONS)
TOOL WEIGHT: 16.1 LBS (7.3 kg)
LENGTH: 16.9 (42.9 cm)
WIDTH: 3.2 (8.1 cm)
HEIGHT: 13.7 (34.8 cm)
OPERATING VOLTAGE: 18V-DC
RECHARGE TIME: 45 MINUTES

FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR SUPERIOR PERFORMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE-HANDED OPERATION FOR ADVANCE, RETRACT AND HOLD.
- 45 MINUTE CHARGER CONTROLS CURRENT, VOLTAGE AND TEMPERATURE TO MAXIMIZE BATTERY LIFE. FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT-IN AIR VENTS.
- STATE OF THE ART "C" SHAPED CRIMPING HEAD DESIGN, 355° ROTATION LETS THE USER GET INTO TIGHT AREAS EASIER.
- DIELESS SYSTEM ELIMINATES THE NEED TO PURCHASE AND MAINTAIN DIES.
- DIELESS SYSTEM ALLOWS CONNECTORS AND SPLICES TO BECOME RANGE TAKING.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES. LANYARD IS STORED UNDER LID IN COVER OF CASE.
- 5 YEAR LIMITED WARRANTY ON THE TOOL, 3 YEAR WARRANTY ON THE BATTERIES AND CHARGER.
- LIFETIME WARRANTY ON THE INFINITY® DRIVE.

PAT444SL5
PAT444SLI



TO ORDER BURNDY® PRODUCTS CALL				PATRIOT PAT444SL5, LI			
UNITED STATES:				ITEM NO: --			
1-800-346-4175 (LONDONDERRY, NH)				CAT. NO: SEE TABLE			
CANADA:				DRAWN BY: T. FAUCHER 02/28/2017			
1-800-361-6975 (QUEBEC)				CHECKER: M. CHIASSON 02/28/2017			
1-800-387-6487 (ALL OTHER PROVINCES)				DSN APPVL: M. CHIASSON 03/01/2017			
FOR PRODUCT INFO: http://www.burndy.com				MFG APPVL: N. CHRISTNACH03/08/2017			
				QA APPVL: C. LINDQUIST 03/02/2017			
				MKT APPVL: --			
				SCALE: 7:32			
				PROD FAM: TOOLS, BATTERY			
				PROJECT #: --			
				DOCUMENT TYPE: Sales			
				REL LEVEL: Released			
				DRAWING NO			
				50076051			
				SHEET 1 OF 1			
				REV			
				C			

REV: PE0200