

131ETTM4TM4-1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	131ETTM4TM4-1
Product ID:	1SNA191532R0500
EAN:	3472591915327
Catalog Description:	BLOC 131 ET TM4-TM4-1-V0 Specific Terminal Blocks

Ordering

Color:	Beige
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	13 mm
Product Net Height:	70 mm
Product Net Depth / Length:	43.5 mm
Product Net Weight:	26 g

Technical

Rated Cross-Section:	6 mm ²
Spacing:	13 mm
Connection Type:	Stud
Function:	Disconnect
Number of Levels:	1
Connecting Capacity Main Circuit:	Stud / Flexible 1x 6 mm ² Stud / Rigid 1x 6 mm ²
Rated Current (I_n):	Main Circuit 41 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 8000 A
Rated Voltage (U_r):	1000 V
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Tightening Torque:	Cable Lug 2.5 N·m

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
	Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225002U1000
Environmental Information:	1SND220051E1002

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	172 mm
Package Level 1 Depth / Length:	155 mm
Package Level 1 Height:	71 mm
Package Level 1 Gross Weight:	0.65 kg
Package Level 1 EAN:	3472591915327
Package Level 2 Units:	250 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Product Packing Type:	Box

