


POTTING BOXES DUROPLASTIC

Plastic enclosures for encapsulating electronics

Comprehensive range of boxes for potting electronic assemblies. With special cost advantages for series type production.

- potted assemblies are protected from shock as well as temperature, dampness and chemical influences
- Duroplast: resistant to deformation and extreme temperatures, less resistant to impact than the PA or ABS models, 19 sizes (0.787" x 0.787" x 0.516" to 3.937" x 3.937" x 1.575"), optional lids available

[Link POTTING BOXES Thermoplast](#)



[View Customizing Options](#)

What do you still need for your own very personal product? We can supply enclosures and tuning knobs with all necessary modifications for fitting your electronic components. Customizing options for Potting Boxes Duroplastic



Machining



Printing



Installation / Assembly
of accessories

POTTING BOXES DUROPLASTIC

Select Versions



A8010250
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
3.94"x1.98"x0.98"




A8010400
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
3.94"x3.94"x1.57"



A8020130
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
0.79"x0.79"x0.52"



A8025150
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
0.98"x0.98"x0.58"




A8025251
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
0.98"x0.98"x0.98"



A8030150
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.19"x0.79"x0.59"



A8040130
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.57"x1.57"x0.50"



A8040160
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.59"x0.54"x0.63"



A8040200
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.58"x1.58"x0.79"



A8040250
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.58"x0.53"x0.98"



A8045150
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.78"x1.19"x0.59"



A8045250
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.78"x1.18"x0.98"



A8050150
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.96"x0.52"x0.59"



A8050160
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.97"x1.97"x0.59"



A8050250
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
1.97"x1.97"x0.99"



A8050500
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
2.00"x2.00"x1.96"

POTTING BOXES DUROPLASTIC



A8070200
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
2.76"x1.98"x0.79"




A8070350
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
2.78"x1.98"x1.38"




A8090200
POTTING BOXES, Vers. I
PF (UL 94 V-0)
black RAL 9005
3.56"x2.37"x0.79"


Accessory to complete




A8130200
Lid 1.181" x 0.787"
PF (UL 94 V-0)
black RAL 9005




A8140130
Lid 1.575" x 0.512"
PF (UL 94 V-0)
black RAL 9005




A8140400
Lid 1.575" x 1.575"
PF (UL 94 V-0)
black RAL 9005



A8145300
Lid 1.772" x 1.181"
PF (UL 94 V-0)
black RAL 9005



A8150500
Lid 1.969" x 1.969"
PF (UL 94 V-0)
black RAL 9005



A8170500
Lid 2.756" x 1.969"
PF (UL 94 V-0)
black RAL 9005

Subject to technical modification without notice. © by OKW Gehäusesysteme, Buchen/Germany.