

D SUB IP 67 MA ANG_PCB_50P_S4_METAL FRAM

[Spotted an error?](#) |  [Print page](#)

[Back >](#)



Image is for illustration purposes only.
Please refer to product description.

[Login to MyHARTING](#)
for pricing and stock check

Quantity:

[Shopping cart >](#)

[Email inquiry >](#)

Catalogue

HARTING Device Connectivity -
Page 378



[Browse](#)

[Download](#)

- [Features](#)
- [Connection data](#)
- [Dimensions and weight](#)
- [Supplementals](#)

Part number:	09 67 650 9658
Description:	D SUB IP 67 MA ANG_PCB_50P_S4_METAL FRAM

Features

Application:	Board Connector Panel Mount
Class of Protection:	IP67
Contact Pitch:	2.54 mm
Gender:	Turned Male Contact
Mating Hardware:	Flange Thread M3
No. of contacts:	50
Performance level:	S4
RoHS conformity:	Yes
Termination Type:	Solder
Type:	Rear Mount Angled Metal Frame

[Top](#)

Connection data

Current:	5 A @ 20°C
----------	------------

[Top](#)

Dimensions and weight

Net Weight:	69.33 g
-------------	---------

[Top](#)

Supplementals

Series:	D-Sub Waterproof
---------	------------------

[Top](#)

Downloads

Title	Download
CAD data 3D	 STEP
CAD data 3D	 JT
HARTING Device Connectivity - Page 378	 PDF

Recently viewed - [Delete](#)



D SUB IP 67 FE
STR_PCB_50P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
STR_PCB_50P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
ANG_PCB_50P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 FE
STR_PCB_50P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
STR_PCB_37P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
ANG_PCB_37P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 FE
STR_PCB_37P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
STR_PCB_37P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
ANG_PCB_37P_S4_METAL
FRAM

[Show product details](#)



D SUB IP 67 MA
STR_PCB_25P_S4_METAL
FRAM

[Show product details](#)

Recently searched

No searches have been done yet.

