




Part Number : [2030703241](#)
Product Description : Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 1.42-2.10mm Insulation Diameter, Reel
Series Number : 203070
Status : Active
Product Category : Crimp Terminals




Documents & Resources

Drawings
[2030703241_sd.pdf](#)
[2030700002-000.pdf](#)

Specifications
[AS-172718-0000-001.pdf](#)
[2131370000-AS-000.pdf](#)
[2029880001-PS-000.pdf](#)
[1727180003-TS-000.pdf](#)
[2029880001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	203070
Description	Mini-Fit TPA2/Sigma Male Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 20-18 AWG, 1.42-2.10mm Insulation Diameter, Reel
Application	Power
Comments	See product specification for current derating information.
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	191128371049

Electrical

Current - Maximum per Contact	13.5A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.192/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.42-2.10mm

Wire Size (AWG)	18, 20
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Plug Housings	<u>172762</u>
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Plug Housings	<u>172767</u>
Mini-Fit Sigma Sealed Dual Row Plug Housings	<u>207017</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 18 AWG, Large and Small Insulation Grips	<u>2002180100</u>
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 20 AWG, Large and Small Insulation Grips	<u>2002182100</u>
FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.50mm ² , 0.75mm ² and 20-18 AWG wires	<u>639036900</u>

This document was generated on Apr 26, 2025