SmartRack 1U Rack-Mount Keyboard with KVM Cable Kit, TAA

MODEL NUMBER: **SRSHELFKBD**



Full keyboard with touchpad mounts in 1U of space in 2- and 4-post racks. Ideal for connecting with KVM switches and servers that don't come with a keyboard.

Highlights

- 104-key keyboard and 2-button touchpad
- Slides in and out of rack for easy access and storage
- Heavy-duty black steel housing
- Compatible with 2- and 4-post rack-mounting
- Includes USB-A cable for connecting to KVM or server

Package Includes

- SRSHELFKBD SmartRack 1U Rack-Mount Keyboard
- KVM cable kit (USB-A)
- Mounting brackets
- Owner's manual

Description

The SRSHELFKBD SmartRack® 1U Rack-Mount Keyboard is a full 104-key keyboard and two-button touchpad designed for mounting in an EIA-standard 19-inch rack. Ideal for use with KVM switches and servers that don't include a keyboard, the SRSHELFKBD comes with a USB-A cable for quick connection. Use the convenient handle to slide the keyboard out of the rack for easy access and slide it back, hidden away, when not in use. Protected by a heavy-duty steel housing with a black finish. Compatible with both two- and four-post racks (a B019-000 bracket is required for 2-post mounting).

Features

104-Key Keyboard and 2-Button Touchpad

- Mounts in 1U of EIA-standard 19 in. racks
- Ideal for KVM switches and servers that don't include keyboard
- USB-A cable included for quick connection
- Slides in and out of rack for easy access and storage
- Heavy-duty steel housing with black finish
- Compatible with 2- and 4-post racks
- B019-000 bracket required for 2-post mounting

Specifications

OVERVIEW	
UPC Code	037332188489
Accessory Type	Keyboard
Accessory Class	Rack Accessories
PHYSICAL	

Downloaded from Arrow.com.

Shipping Dimensions (hwd / in.)	5.91 x 20.47 x 22.83
Shipping Dimensions (hwd / cm)	15.01 x 51.99 x 57.99
Shipping Weight (lbs.)	24.00
Shipping Weight (kg)	10.89
Unit Dimensions (hwd / in.)	1.710 x 18.820 x 21.750
Unit Dimensions (hwd / cm)	4.34 x 47.80 x 55.25
Unit Weight (lbs.)	19.6
Unit Weight (kg)	8.89
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.