USB4715 - IP67 Type C USB Charging Connector



Some images above show USB4715 with gasket USBTJ-04, ordered separately. Connector and gasket available as a kit from selected distributors (USB4715-GF-A-KIT).

Product overview

Active

convert to inches

- Series : USB4715
- Product Family : USB Charging Connector | View similar USB connectors
- Connector style : Type C
- Interface : C
- USB version : Charging
- Gender : Receptacle (socket)
- Waterproof : IP67
- Number of contacts : 6
- PCB mount type : Surface Mount
- Orientation : Horizontal
- Entry type : Side
- Profile : 4.00mm
- Offset height : 0.55mm
- Mount position : Mid Mount
- Elevated : No
- Voltage Rating : 48V DC
- Current Rating : 3A
- Mating face style : N/A
- Shell stake : Through Hole
- Shell stake lengths : 0.80mm
- Locating Peg : Without
- Mating Cycles : 20000
- Body Length : 8.20mm
- Additional Information : For IP67 performance, USBTJ-04 gasket ordered separately.


View Product Drawing | View Product Spec | Test Reports | Request Quote | Distributor Stock

Product Resources

3D Model Generator | Electrical Models / PCB Footprints | Product Drawing | Specification Overview | Product Spec | PCNs | Test Reports | Product Video | Compliance Certificate | FMD

USB4715-GF-A

Company	Global Connector Technology
Description	USB4715
Bill of material	USB4715-GF-A
Order Code	USB4715-GF-A
Website Link	https://gct.co/connector/usb4715
Contact Plating	GF = Gold Flash
Packaging Options	A = Tape & Reel
Revision	A
Revision Date	04.07.2022
GCT Disclaimer	The creation and usage of 3D models generated by this builder are covered in our disclaimer which can be viewed here



©2026 powered by CADENAS

Download CAD

powered by CADENAS | Legal notice | Terms and Conditions | Terms of Use | Data privacy policy | Cookie settings | DE-230

Authorised distributors for USB4715-GF-A-KIT

DigiKey	DigiKey	9694 In stock	1 Min order	BUY NOW
Mouser Electronics	Mouser Electronics	3657 In stock	1 Min order	BUY NOW
TME	TME	809 In stock	1 Min order	BUY NOW
Future Electronics	Future Electronics	No stock	700 Min order	REQUEST
Rutronik	Rutronik	No stock	700 Min order	REQUEST
Farnell UK	Farnell UK	No stock	1 Min order	REQUEST
element14	element14 Singapore	No stock	1 Min order	REQUEST
Newark	Newark	No stock	1 Min order	REQUEST
Heilind Europe	Heilind Europe	No stock	700 Min order	REQUEST
Future Electronics	Future Electronics EMEA	No stock	700 Min order	REQUEST

Authorised distributors for USB4715-GF-A

Mouser Electronics	Mouser Electronics	1929 In stock	1 Min order	BUY NOW
Heilind Europe	Heilind Europe	700 In stock	700 Min order	BUY NOW
Heilind Americas	Heilind Americas	525 In stock	700 Min order	BUY NOW
DigiKey	DigiKey	357 In stock	1 Min order	BUY NOW
Farnell UK	Farnell UK	32 In stock	1 Min order	BUY NOW
Newark	Newark	21 In stock	1 Min order	BUY NOW
element14	element14 Singapore	21 In stock	1 Min order	BUY NOW
Future Electronics	Future Electronics	No stock	700 Min order	REQUEST
Future Electronics	Future Electronics EMEA	No stock	700 Min order	REQUEST
TME	TME	No stock	700 Min order	REQUEST

Authorised distributors for USB4715-GF-A-CUT

Questions?

Our customer support are available to answer any questions you may have

Contact us

Back to Top

Be in the know about product launches, promotions and more

Sign up to get the latest news *

Submit

By submitting your email, you are agreeing to receive occasional updates from GCT.

About: news, company, careers, GCT connect

Useful: rep/distributor, get in touch

Support: quality and compliance, cross ref

Global headquarters

GCT Limited
Alchemy, Bessemer Road, Welwyn Garden City, Hertfordshire, AL7 1HE
United Kingdom
sales@gct-europe.com
+44 (0)1707 321122

GCT Inc
354 Merrimack Street, Building 1, Suite 262, Lawrence, Massachusetts, 01843
United States
sales@gct-americas.com
+1 978 208 1618

GCT Hong Kong Ltd
Unit B, 8/F, Hang Cheong Factory Building, 1 Wing Ming Street, Cheung Sha Wan
Kowloon, Hong Kong
sales@gct-apac.com
+852 2578 9030

Regional offices

Singapore, SG
sales@gct-apac.com
+65 8332 2263

New Delhi, IN
sales@gct-apac.com
+91 987 300 8975

Boston, MA, USA
sales@gct-americas.com
+1 978 208 1618

San Jose, CA, USA
sales@gct-americas.com
+1 650 448 9660

Berlin, DE
salesde@gct-europe.com
+49 162 301 4214

GCT better connected

Privacy Policy | Legal and Terms

Copyright © 2026 GCT (Global Connector Technology) All Rights Reserved

Downloaded from Arrow.com.